



Dimensions (In.)
(except where noted)

Specifications:

- Type: subminiature thumbwheel
- Rated wattage: .1W(linear taper), .05W(audio taper)
- Rated voltage: 200V(linear taper), 150V(audio taper)
- Total rotation angle: 260°±5°
- Shaft stop strength: More than 3Kgf.cm/min.
- Rotation torque: 20~200 gf.cm
- Switch circuit: S.P.S.T.
- Switch rating: 12VDC, 1A
- Switch working angle: 30°±10°
- Rotational life: 15,000 cycles

Audio Taper with Switch

Stock No.	Value (Ω)
31TV205	500
31TV301	1K
31TV302	2K
31TV305	5K
31TV401	10K
31TV405	50K
31TV501	100K
31TV505	500K
31TV601	1M

Linear Taper with Switch

Stock No.	Value (Ω)
31XT205	500
31XT301	1K
31XT305	5K
31XT401	10K
31XT405	50K
31XT501	100K
31XT505	500K
31XT601	1M