



## IEC Connector IEC60320 Sheet F

# 0718-1 Series


**Power Rating :** 10A 250V AC

**Insulation Resistance :** over 100MΩ 500V DC

**Withstanding Voltage :** 2,000V AC One Minute


**Operating Rating Temperature :** -25°C to +85°C

**Main Unit Material :** Thermoplastic UL Flammability  
94V-0 & Copper Alloy




## Power Outlet


Unit:mm







THICKNESS:  
0.8-1.2t (X=25.2)  
1.3-2.0t (X=25.4)






PANEL CUT-OUT



PCB LAYOUT



ORDER NO.	CODE	TERMINAL OPTION
0718-1-PN	N	4.0mm/SOLDER TAB 
0718-1-PQ	Q	4.8mm/.187" Q.D./SOLDER TAB 
0718-1-PW	W	6.3mm/.250" FAST-ON TAB 
0718-1-PP	P	FOR PCB. MOUNTING 