

# SPECIFICATION FOR APPROVAL

CUSTOMER: JAMES

PART NO:

MODEL NO: 3.5x1.3Plug + 3.5x1.3Jack AWG#18 105°C 3FT

DESIGNED NO: V0220 RoHS

REVISION: 1-0

CATEGORY: DC CORD

DATE SUBMITTED: 2018.03.13

SAMPLE/SPECIFICATION SUBMITTED		CONCLUSION	APPROVED
SAMPLE	2		REJECTED
SPECIFICATION	1		CONDITION APP'D

CUSTOMER'S SIGNATURE:

浩源實業有限公司  
HAWK'S AIM INDUSTRIAL CO., LTD.  
高雄市前鎮區新衙路 286-8 號 5F-2  
5F-2, No. 286-8, Shin-Ya Road, Chien-Chen  
District, Kaohsiung, Taiwan 806  
Tel: 07-8418448 Fax: 07-8419997

MODEL NO: 3.5x1.3Plug + 3.5x1.3Jack AWG#18 3FT

CUSTOMER P/N:

DESCRIPTION: DC CORD

ISSUED DATE: 2018.03.13

REVISION: 1-0

TABLE OF CONTENTS

1.0 APPEARANCE DIMENSION

REV	DESCRIPTION	DATE
1-0	INITIAL RELEASED	2018.03.13


APP.BY \_\_\_\_\_

CHK.BY \_\_\_\_\_

PRE.BY \_\_\_\_\_

1.0 APPEARANCE DIMENSIONS: (UNIT:mm)

DC CORD COLOR: BLACK



BLACK WIRE —●— LETTERED WIRE

BLACK WIRE —●— LETTERED WIRE

FUNCTION TEST: No open, no reversed polarity, no short-circuit, no INT  
 CABLE ASSEMBLY SHALL BE IN COMPLIANCE WITH RoHS REQUIREMENT.  
 HI-POT: 600VAC,0.5mA,1Second

APP.BY \_\_\_\_\_

CHK.BY \_\_\_\_\_

PRE.BY \_\_\_\_\_