



Solder Terminal  
(Ratio 5:1)



1. Rating : AC 125V 4A 250V 2A
2. Contact R. : 50mΩ Max.
3. Insulation R. : DC 500V 100MΩ Min.
4. Dielectric Strength : AC 1500V 1 minute.
5. Electrical Life : 50,000 make-and-break cycles at full load.
6. Operating temperature : -20°C~65°C

Item#	01-690A/B/C (NEW)	Part#	PB-4166-1	Rev.	0
Modify	Date	Revision	Approval	No.	Title
					Stomp Foot Pedal Switch
					Part
					Mat'l
					Finish
					Unit
					m/m
					Ratio
					1.2:1
Size	0.5-6	>6-30	>30-120	>120-400	Auth
Tol	+/-0.05	+/-0.1	+/-0.15	+/-0.2	max
					CHK
					Derek
					DWG
					Angela
					Date
					2017/10/24
					Proj.
					3rd

CIC COMPONENTS IND. CO., LTD.