

1

2

3

4




5

# BTS-S1104(L)5-(OF)-(RP)-DYL



Type	1	2	3
Operating Force	100±50gf	160±50gf	260±50gf
Return Force	20gf min	40gf min	60gf min

Package:  
RP : Taping Reel Package

Model.No.	1104	1104AC	1104A	1104AA	1104AB	1104AN	1104C	1104R	1104D
L(mm)	4.3	4.5	5.0	6.0	7.0	7.5	8.0	9.0	9.5



PCB Layout(Pattern side)



- Rating: DC12V 50mA
- Contact Resistance : 50mΩ max(Initial)
- Insulation Resistance: 100MΩ
- Electrically Life:100gf 100,000 cycles  
160gf 80,000 cycles  
250gf 60,000 cycles
- Travel:0.25±0.1mm

自由公差	公差
区分	公差
0	±0.10
0.50	±0.15
5.0	±0.20
10.0	±0.30
20.0	±0.40
未标注R角	R0.3
未标注角度公差	±2°

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Terminal	2	Brass(0.30t)	Plating silve
④	Contact	1	F.Ag/SUS	Plating silve
③	Base	1	Nylon	Black
②	Cover	1	SPCC	Plating Nicke
①	Keystoke	1	Nylon	Black

單位	比例	日期	核准	審核	設計繪圖	料號	頁數
mm	Free	2016-12-21	William	Amy	DYL	BTS-S1104(L)5-(OF)-(RP)-DYL	1/1

TOP WILLING CO., LTD.

1

2

3

4

5