

## Multi-Conductor Unshielded UL 2464 - 22 AWG

### Product Details

- Unshielded Multi-Conductors with Gray PVC Jacket and Annealed Stranded Tin Copper Conductor
- Insulation Thickness .010"
- Rated 300V Temp: 2464 UL: 80C CM: 75C
- UL 2464 CM CSA FT1 UL VW-1

Part Number	Construction	C/PR	Insulation	Jacket Material	Jacket Thickness	Nom. OD (in)	Style	Color Code
5400-CL	22 (7x30) TC	2C	PVC	PVC	.030	.161	CM / UL 2464	<u>1</u>
5401-CL	22 (7x30) TC	3C	PVC	PVC	.030	.163	CM / UL 2464	<u>1</u>
5406-CL	22 (7x30) TC	4C	PVC	PVC	.030	.177	CM / UL 2464	<u>1</u>
5411-CL	22 (7x30) TC	5C	PVC	PVC	.030	.198	CM / UL 2464	<u>1</u>
5416-CL	22 (7x30) TC	6C	PVC	PVC	.030	.211	CM / UL 2464	<u>1</u>
5421-CL	22 (7x30) TC	7C	PVC	PVC	.030	.212	CM / UL 2464	<u>1</u>
5426-CL	22 (7x30) TC	8C	PVC	PVC	.030	.228	CM / UL 2464	<u>1</u>
5431-CL	22 (7x30) TC	9C	PVC	PVC	.030	.235	CM / UL 2464	<u>1</u>
5432-CL	22 (7x30) TC	10C	PVC	PVC	.030	.263	CM / UL 2464	<u>1</u>
5434-CL	22 (7x30) TC	12C	PVC	PVC	.030	.273	CM / UL 2464	<u>1</u>
5438-CL	22 (7x30) TC	15C	PVC	PVC	.030	.294	CM / UL 2464	<u>1</u>
5440-CL	22 (7x30) TC	20C	PVC	PVC	.035	.330	CM / UL 2464	<u>2</u>
5442-CL	22 (7x30) TC	25C	PVC	PVC	.035	.356	CM / UL 2464	<u>1</u>
5446-CL	22 (7x30) TC	30C	PVC	PVC	.035	.390	CM / UL 2464	<u>1</u>
5448-CL	22 (7x30) TC	40C	PVC	PVC	.035	.423	CM / UL 2464	<u>1</u>
5450-CL	22 (7x30) TC	50C	PVC	PVC	.035	.490	CM / UL 2464	<u>1</u>
5460-CL	22 (7x30) TC	60C	PVC	PVC	.035	.520	CM / UL 2464	<u>2</u>

### Consolidated Color Code Chart #1 - Conductors

No. Of Cond.	Color	No. Of Cond.	Color	No. Of Cond.	Color
1	Black	2	Red	3	Green
4	White	5	Brown	6	Blue
7	Orange	8	Yellow	9	Purple
10	Slate	11	Pink	12	Tan

### Consolidated Color Code Chart #2 - Conductors

No. Of Cond.	Color	No. Of Cond.	Color	No. Of Cond.	Color
--------------	-------	--------------	-------	--------------	-------

No. Of Cond.	Color	No. Of Cond.	Color	No. Of Cond.	Color
1	Black	2	White	3	Red
4	Green	5	Orange	6	Blue
7	White/Black	8	Red/Black	9	Green/Black
10	Orange/Black	11	Blue/Black	12	Black/White
13	Red/White	14	Green/White	15	Blue/White
16	Black/Red	17	White/Red	18	Orange/Red
19	Blue/Red	20	Red/Green	21	Orange/Green
22	Black/White/Red	23	White/Black/Red	24	Red/Black/White
25	Green/Black/White	26	Orange/Black/White	27	Blue/Black/White
28	Black/Red/Green	29	White/Red/Green	30	Red/Black/Green
31	Green/Black/Orange	32	Orange/Black/Green	33	Blue/White/Orange
34	Black/White/Orange	35	White/Red/Orange	36	Orange/White/Blue
37	White/Red/Blue	38	Black/White/Green	39	White/Black/Green
40	Red/White/Green	41	Green/White/Blue	42	Orange/Red/Green
43	Blue/Red/Green	44	Black/White/Blue	45	White/Black/Blue
46	Red/White/Blue	47	Green/Orange/Red	48	Orange/Red/Blue
49	Blue/Red/Orange	50	Black/Orange/Red	51	White/Black/Orange
52	Red/Orange/Black	53	Green/Red/Blue	54	Orange/Black/Blue
55	Blue/Black/Orange	56	Black/Orange/Green	57	White/Orange/Green
58	Red/Orange/Green	59	Green/Black/Blue	60	Orange/Green/Blue

**Note: All specifications are subjected to change without prior notice.**