





Date	Rev.	Description

	PARTS NAME	THE PARTS OF MATERIAL	ELECTROPLATING	RoHS No
1	Slide Handle	Brass	Nickel Plating	RoHS
2	Spring	Steel wire	-----	RoHS
3	Bushing	Brass	Nickel Plating	RoHS
4	Supporting Halt	Brass	-----	RoHS
5	Sliding Point	Bakelift	-----	RoHS
6	Housing	Bakelift	-----	RoHS
7	Movable Plate	Brass	Silver Plating	RoHS
8	Terminals	Brass	Silver Plating	RoHS
9	Nuts	Brass	Nickel Plating	RoHS
10	Zigzag Washer	Stainless Steel	-----	RoHS
11	Fix Washer	Stainless Steel	-----	RoHS
12	Steel crust	Stainless Steel	-----	RoHS
13	Epoxy Seal	5010A/B	-----	RoHS



Circuit Diagram

Specification

Rating: 2A 250V AC ; 5A 125V AC
 Contact R: 20 mΩ Max
 Insulation R: DC500V 1000MΩ Min
 Dielectric strength: 1500V AC, 1minute
 Electrical life: 10,000 Cycles

MATERIAL
DRAWN: Ivan Wang
VERIFY PEOPLE: Jenny

GOLDSUN ELECTRONICS CO., LTD.			
JAMECO NO.	22833-100	GOLDSUN NO.	GS-10261
Description	MINI TOGGLE SWITCH ON-ON SPDT 3P SOLDER LUGS, FLAT		Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No:

DCC. NO.
A4 DRAWING NO.