



Declaration of RoHS & PFOS Conformity

To minimize the environmental impact and take more responsibility to the earth we live, MEAN WELL hereby confirms that the following product series comply with Directive of the European Parliament 2011/65/EU、2015/863/EU - ROHS (Restriction of Hazardous Substances) and 2006/122/EC - PFOS (PerFluoroOctane Sulfonates)

Content of Compliance

Lead (Pb)	<0.1 % by weight (1000 ppm)
Mercury (Hg)	<0.1 % by weight (1000 ppm)
Cadmium (Cd)	<0.01 % by weight (100 ppm)
Hexavalent Chrome (Cr ⁶⁺)	<0.1 % by weight (1000 ppm)
Polybrominated Biphenyls (PBBs)	<0.1 % by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDEs)	<0.1 % by weight (1000 ppm)
Bis(2-ethylhexyl) phthalate (DEHP)	<0.1 % by weight (1000 ppm)
Butyl benzyl phthalate (BBP)	<0.1 % by weight (1000 ppm)
Dibutyl phthalate (DBP)	<0.1 % by weight (1000 ppm)
Diisobutyl phthalate (DIBP)	<0.1 % by weight (1000 ppm)
Decabromobiphenyl(DecaBDE)	n.d. (Not Detected)
PFOS	<0.1 % by weight (1000 ppm)

Product Series

Please refer to the attached list for details.

Delivery

Products announced to be RoHS and PFOS compliance can be provided now. Please contact our sales representatives for details.

Jerry Lin / President
MEAN WELL Enterprises Co., Ltd

Product Family	Series
G3	RS-15/25/35/50/75/100/150, RD-35/50/65/85/125, RID-50/65/85/125, RT-50/65/85/125, RQ-50/65/85/125
G2/SE/LRS	S-25/40/60/100F/150/210/250/320, T-40, D/ID/T/IT/Q/IQ-60, D/T/Q-120, SC-150, SE-100/200/350/450/600/1000/1500,LRS-35/50/75/100/150/150F/200/350
LED Sign Panel	ERP-350, HSN-200/300, NEL-200/300/400, HSP-150/200/250/300, HDP-190/240, ERPF-400, UHP-200A/200(R)/350(R)/ 500(R),LHP-200
PFC	SP-75/100/150/200/240/320/480/500/750, USP-150/225/350/500, TP-75/100/150, QP-100/150/200/320/375, PSP-500/600, PSPA-1000, RSP-75/100/150/200/320/500/750/1000/1500/1600/2000/2400/3000, RST-5000/10000, SPV-150/300/1500, HRP-75/100, HRP(G)-150/200/300/450/600, HRPG-1000, MSP-100/200/300/450/600/1000, HEP-100/150/185/240/320/480/600, DPU-3200
LED	HLG-40H/60H/80H/100H/120H/150H/185H/240H/320H/480H-(C), HLG-600H, CLG-60/100/150, POB, RFP, NCL, HSG-70, FDL-65, CEN-60/75/100, DLP-04, HVG(C)-65/100/150/240/320/480/650, ELG-75/100/150/200/240, ELG-75/100/150/200/240-C, ELGT-150-C, ELGC-300, LDV-185, FDLC-80/100, GSC18/25/40, SDP-001, IRL, OWA-60/90/120, HBG-60(P)/100(P)/160(P)/200/240(P), HBGC-300, ULP-150, APV-8(E)/12(E)/16(E)/25/35, NPF-40(D)/60(D)/90(D)/120(D), HLN-40H/60H/80H, LDB, PLN-20/30/45/60/100, PLC-30/45/60/100, PLM-12(E)/25(E)/40(E), PCD-16/25/40/60, IDLV-25/45/65, DAP-04(S01), SPD-20(HP), LDH-45(DA), LDD-DA, IDLC-25/45/65, IDPV-25/45/65, IDPC-25/45/65, ODLC-45/65, LDD-L/H, ELN-30/60 ODLV-45/65, PLD-16/25/40/60, LPH(C)-18, LCM-25(DA)/40(DA)/40U(DA)/60(DA)/60U(DA), APC-8(E)/12(E)/16(E)/25/35, LPVL-150, LDC-35/55/80(DA), LCM-40/60(U)EO, PWM-40/60/90/120, HLP-40H/60H/80H, LPF-16(D)/25(D)/40(D)/60(D)/90(D), LPFH-60(D), PLP-20/30/45/60, LPL(C)-18, LPV(C)-20/35/60/100/150,
DIN	DRA-40/60, MDR-10/20/40/60/100, DR-15/30/45/60/75/100/120, DRH-120, DRP-240/480/480S, DRT-240/480/960, HDR-15/30/60/100/150, DR-UPS40, EDR-75/120/150, NDR-75/120/240/480, SDR-75/120/240/480(P)/960, WDR-120/240/480, TDR-240/480/960, DR-RDN20, KNX-20E-640, KDA-64, KSI-01U, KSR-01IP, KSC-01L
Modular	MP450/650/1K0, MS-75/150/210/300/360, MD-100, NMP650/1K2, NMS-240
19' Rack Power	RCP-1000/1600/2000, RCP-1U, RKP-1U, RHP-1U, RCP-MU, RKP-CMU1, RKP-1U-CMU1, DRP-3200, DHP-1UT
Open Frame	NFM-05/10/15/20, MFM-05/10/15/20/30, PM-05/10/15/20, PS-05/15, MPM-05/10/15/20/30/30ST, PS/PD-25, PS-35, PS/PD/PT-45/65, RPD/RPT-65, PD-110, PQ-100, PPQ-100, PPS-125/200, PPT-125, LPS-50/75/100, LPP-100/150, ASP-150, PID-250, ELP-75, MPS/MPD/MPT/MPQ-120/200, RPT-160-C, RPS-120/200/300(-C), RPS-400/500(-C/-TF/-SF), IRM-01(S)/02(S)/03(S)/05/10/15/20/30(ST)/45(ST)/60(ST), RPS/RPD/RPT-65/75, RPS/RPD/RPT-60, EPS-15/25/35/45S/45(C)/65S/65(C)/120, EPP-100/150/200/300/400/500, MPS-30, MPS/MPD/MPT-45/65, RPS-30/45/65, RPS(G)/RPD(G)/RPT(G)-160
Charger	GC30/120/160/220/330, PA/PB/PS-120, ESC/ESP-120/240, PB-230/300/360/600/1000, HEP-600C, RPB-1600, RCB-1600, ENP/ENC-120/180/240/360, DBU-3200, DBR-3200, DHB-1UT
Adaptor	GS05/06/12/15/18/25/36/40/60/90/120/160/220/280, GE12/18/24/30, ES18/25, P25/50, GP25/50, MES-30/50, GEM12I/18I/30I/40I/60I, GSM06/18/25/36/40/60/90/120/160/220, GST18/25/36/40/60/90/120/160/220/280, SGA12/18/25/40/60
Security	SCP-35/50/75, ADS-55/155, AD-55/155, ADD-55/155, PSC-35(C)/60(C)/100(C)/160(C), DRC-40/60/100
ATX / Gaming Power	YP-350J, YP-350A/400A/450A, IPC-200/250/300, MWP-610(P)
DC/DC Converter	SD-15/25/50/100/150/200/350/500/1000, RSD-30/60/100/150/200/300, SDM30, NSD, NID, PSD, SBT, SFT, DET, SRS, SUS, SPR, SMU, SMA, SPU, SPA, SPB, SCW, SLW, SKE, SKA, SKM, DCW, DLW, DKE, DKA, TKA, MHB, ,DPU, SPAN, DPAN, SPBW, DPBW, SLC, DLC, SCWN, DCWN, DKM, SKMW, DKMW, MDS, MDD, SBTN, SFTN, DETN, ,DDR-15/30/60/120/240, RSDW/RDDW08/10/20
Inverter	TS-200/400/700/1000/1500/3000, TN-1500/3000, A301/A302, IRC1/2/3, ISI-500/501, GSI-3000/4600/5000
Power Cord	YP** + YC**
Accessories	DRL, DRP, MHS, TBC, FAP, FAS

**** For other products not listed above, please contact our sales representatives for availability**

2018.07.01 updated