

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 228478

RCA Audio Patch Cords

Shielded RCA Patch Cords
 Black 2.8mm OD PVC Jacket
 Fully Molded Construction
 Nickel or Gold-Plated High-Retention RCA Plugs
 Color-Coded Red-White/Red-White or Black-Black
 AWG26 Stranded Copper Center Conductor
 Low-Loss 95% Spiral-Wound Copper Shield
 99.99% Pure Oxygen-Free Copper Wire

- 255-100** 6' RCA Jack to RCA Plug
- 255-105** 10' RCA Jack to RCA Plug
- 255-110** 6' RCA Plug to RCA Plug
- 255-115** 10' RCA Plug to RCA Plug
- 255-117** 25' RCA Plug to RCA Plug
- 255-118** 25' RCA Plug to Plug – AWG24
- 255-120** 3' 2-RCA Plugs to 2-RCA Plugs
- 255-121** 3' 2-RCA Plug-Plug Gold Plated
- 255-125** 6' 2-RCA Plugs to 2-RCA Plugs
- 255-126** 6' 2-RCA Plug-Plug Gold Plated
- 255-127** 9' 2-RCA Plugs to 2-RCA Plugs
- 255-128** 9' 2-RCA Plug-Plug Gold Plated
- 255-130** 12' 2-RCA Plugs to 2-RCA Plugs
- 255-131** 12' 2-RCA Plug-Plug Gold Plated
- 255-132** 15' 2-RCA Plugs to 2-RCA Plugs
- 255-133** 15' 2-RCA Plug-Plug Gold Plated
- 255-134** 20' 2-RCA Plugs to 2-RCA Plugs
- 255-135** 25' 2-RCA Plugs to 2-RCA Plugs
- 255-136** 25' 2-RCA Plug-Plug Gold Plated
- 255-138** 50' 2-RCA Plug-Plug Nickel Plated **◀ NEW**
- 255-140** 6' 2-RCA Plugs – RCA Piggyback
- 255-145** 12' 2-RCA Plugs – RCA Piggyback
- 255-150** 6' 4-RCA Plug-Plug – Color Coded
- 255-175** 6' 2-RCA Jacks to 2-RCA Plugs
- 255-244** 3' 2-RCA Plugs to 2-RCA Angle Plugs
- 255-246** 6' 2-RCA Plugs to 2-RCA Angle Plugs

Black

255-100 6' Nickel
255-105 10' Nickel

Black

255-118 25' AWG24 Nickel

Red

White

Red

White

255-140 6' Nickel
255-145 12' Nickel

Red

White

Yellow

Black

Red

White

Yellow

Black

255-150 6' Nickel

Red

White

Red

White

255-175 6' Nickel

Black

255-110 6' Nickel
255-115 10' Nickel
255-117 25' Nickel



Red

White

Red

White

255-120 3' Nickel
255-121 3' Gold
255-125 6' Nickel
255-126 6' Gold
255-127 9' Nickel
255-128 9' Gold
255-130 12' Nickel
255-131 12' Gold
255-132 15' Nickel
255-133 15' Gold
255-134 20' Nickel
255-135 25' Nickel
255-136 25' Gold
255-138 50' Nickel

Red

White

Red

White

255-244 3' Nickel
255-246 6' Nickel