



Model 1452
Adapter-Binding Posts to BNC Receptacle



Model 1452
Adapter-Binding Posts to BNC Receptacle



Features

- Permits single or double banana plugs to be used with equipment having a BNC male.
- Cross holes .166 (4.2) dia. in body provide side stack up connections.

Materials

Upper Connector: Binding Posts, Insulated.

Material: Binding Post body, brass H.H. per QQ-B-626, Alloy 360.

Finish: Nickel plated per QQ-N-290, class 2 (.0002 min.).

Insulation: Acrylonitrile-Butadiene-Styrene, molded to Binding Posts and BNC receptacle.

Color: One Red and one Black (Gnd).

Operating Temperature: +115°C. (+239°F.) Max.

Marking: "POMONA 1452"

Lower Connector: BNC receptacle, comparable to UG 1094/U.

Finish: Body and fittings, tarnish resistant

Nominal Impedance: 50 Ohms

Specifications

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: Hand-held testing: 30 VAC/60 VDC Max.

Hands free testing in controlled voltage environments: 500 VRMS

Ordering Information

Model: 1452

USA: Sales: 800-490-2361
Technical Support: technicalsupport@pomonatest.com
Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.