


11.75(MIN)

$L \pm Tmm$



Electrical Test:


1. 100%Test(Open, short, miss wire)
2. Contact Resistance: 2 ohm max.
3. Insulation Resistance: 10M ohm min.
4. Hi-pot: 300V DC/10ms

Table:

Length	Part No.
915±30mm	10U3-32103-E-BK
1830±40mm	10U3-32106-E-BK
3050±50mm	10U3-32110-E-BK
4575±50mm	10U3-32115-E-BK

Pin Assignment

Conn.1	Conn.2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
Shell	Shield



⑤	Inside Molding: PE	3	g
④	Outside Molding: 45P PVC Color: Black	16	g
③	USB 3.0 A Type F Pin Gold Plated, Shell Nickel, Blue Insulation	Set	
②	USB 3.0 A Type M Pin Gold Plated, Shell Nickel, Blue Insulation	Set	
①	Super High Speed USB 3.0 Cable UL2725 (7/0.127T*1P+AL+D+MY)*2C+7/0.127T*1P +7/0.2T*2C+AL+MY+DW+BD OD:5.5±0.2mm Color: Black	L	M

REV.	DESCRIPTION	DATE
①	TOLERANCE INCHES M/M	
.X	.015 .30	
.XX	.010 .10	
.XXX	.005 .05	
TITLE: USB 3.0 AM TO AF Extension Cable		
CUSTOMER :		
DRAWN BY		
CUSTOMER NO.:		
CHECK BY		
SCALE NONE DRAWING NO.:		
UNIT MM		
DATE 10U3-321XX-E		

NO.	DESCRIPTION	Q'TY	UNIT	APPD BY	DATE	REV.
						1/1