


Specifications

Current Rating:3.0A AC/DC
 Voltage Rating:250V AC/DC
 Contact Resistance:20mohm Max
 Insulation Resistance:1000Mohm Min
 Withstanding Voltage:600V AC For one minute
 Operating Temperature Range : -40°C to +105°C
 Material:

Plastic:PBT (UL94V-0) Δ
 Standard Color:Black
 Contact:Copper Alloy
 Plating:Gold Plated
 How to order

2216S-XXG-02



Notes:

No. Of Positions 60&64 With Three key;
 All Other Pln With one key.

No. of Positions	Dim A	Dim B	No. of Positions	Dim A	Dim B
6	27.12	5.08	26	52.52	30.48
8	29.66	7.62	30	57.60	35.56
10	32.20	10.16	34	62.68	40.64
12	34.74	12.70	40	70.30	48.26
14	37.28	15.24	50	83.00	60.96
16	39.82	17.78	60	95.70	73.66
20	44.90	22.86	64	100.78	78.74
24	49.98	27.94			

P.C.B Layout

RoHS Compliant

F				DRAWN:	GENERAL TOLERANCE:	繼德工業股份有限公司 Neltron Industrial Co., Ltd.	DESCRIPTION: 2.54mm Shrouded Header With Long Ejector Straight Type	SIZE
E			Jerry Chen	.X=±0.20 .XX=±0.15				
D				CHECKED:	UNIT: MM	PART NO:	A4	
C	02-May-2012	ECN-CN1205001	Andrew	Jeremy Liu	SCALE:1:1			
B	05-JUN-2008	ECN-CN080607	Yangxia		SHEET: 1 / 1	2216S-XXG-02		
A	11-May-2006	(PC0001)	ZHW	APPROVAL:	PROJECTION:			
REV	DATE	FILE	BY	Mike Wu				