



**GARDTEC**

Part Number:

**HP75-36** ("45°" Plug)

Wire: SPT1 2 conductor 105°C, 300 volts

Lengths: 36" (914mm)

Other options:

- terminal connections (any)
- heat shrink
- labeling
- stripping
- tinning
- three conductor cords
- complete wire harness assemblies (rated at 105°C, 300 volts)
- red tracer cords (all head configurations and lengths)

Listings:



UL listed (E189621, E156798)  
Rated 10 AMP/125 VAC

