



UL Style 1007/1569 Hook-up Wire

Consolidated
ELECTRONIC WIRE & CABLE

Product Details:

- Available in Tin Copper or Topcoat
- PVC (Polyvinylchloride) Insulation,
- 1007 80°C & 1569 105°C, 300V
- UL, CSA VW-1 AWM I A/B FT-1

Color Code:

- 0: Black
- 1: Brown
- 2: Red
- 3: Orange
- 4: Yellow
- 5: Green
- 6: Blue
- 7: Violet
- 8: Gray
- 9: White

Custom colors and striping available upon request.

Consolidated Electronic Wire & Cable

 11044 King St.
Franklin Park, Illinois 60131

 800-621-4278

 www.conwire.com

Part Number	Construction	Insulation	Insulation (in)	Nom. OD (in)	Temp.	Volt.	Product Type
827	10 (105x30) TC	PVC	.016	.157	105	300	1569 / 1007
1569101T	10 (Solid) TC	PVC	.016	.134	105	300	1569
826	12 (65x30) TC	PVC	.016	.124	105	300	1569
1569121T	12 (Solid) TC	PVC	.016	.114	105	300	1569
825	14 (41x30) TC	PVC	.016	.105	105	300	1569 / 1007
1569141T	14 (Solid) TC	PVC	.016	.097	105	300	1569
824	16 (26x30) TC	PVC	.016	.092	105	300	1569 / 1007
1569161T	16 (Solid) TC	PVC	.016	.083	105	300	1569
843	18 (16x30) F	PVC	.016	.083	105	300	1569 / 1007
822	18 (16x30) TC	PVC	.016	.080	105	300	1569 / 1007
841	18 (Solid) TC	PVC	.016	.072	105	300	1569 / 1007
820	20 (10x30) TC	PVC	.016	.070	105	300	1569 / 1007
833	20 (7x28) F	PVC	.016	.071	105	300	1569 / 1007
811	20 (Solid) TC	PVC	.016	.064	105	300	1569 / 1007
823	22 (7x30) F	PVC	.016	.063	105	300	1569 / 1007
818	22 (7x30) TC	PVC	.016	.062	105	300	1569 / 1007
801	22 (Solid) TC	PVC	.016	.057	105	300	1569 / 1007
813	24 (7x32) F	PVC	.016	.057	105	300	1569 / 1007
817	24 (7x32) TC	PVC	.016	.056	105	300	1569 / 1007
803	24 (Solid) TC	PVC	.016	.053	105	300	1569 / 1007
806	26 (7x34) F	PVC	.015	.051	105	300	1569 / 1007
815	26 (7x34) TC	PVC	.016	.051	105	300	1569 / 1007
807	26 (Solid) TC	PVC	.015	.048	105	300	1569 / 1007
814	28 (7x36) TC	PVC	.016	.047	105	300	1569 / 1007

Note: All specifications are subjected to change without prior notice.