



ITEM NO.	Length "L"	Length "X"
8102-66107	2130mm	2150mm
8102-66114	4270mm	4290mm
8102-66125	7620mm	7640mm

8025-18			
P1		P2	
1	—————	1	BLUE
2	—————	2	YELLOW
3	—————	3	GREEN
4	—————	4	RED
5	—————	5	BLACK
6	—————	6	WHITE

*NOTE: ALL relevant materials complied with RoHS directive

2	NON-UL 6C 28AWG CONDUCTOR CCA, FLAT TELEPHONE, OD 2.4*6.8mm, JACKET SILVER-GREY DRAWING No. ET002806C-163	Xmm	M304
1	6P6C MODULAR PLUG, GOLD FLASH ON CONTACTS FLAT TYPE	2	M205
No.	DESCRIPTION	Q'TY	Supplier
APPROVED		Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm	
CHECKED			
DRAWING			
DATE	06/JAN/11	ITEM NO.	8102-661XX
		UNIT:mm	

CHECKED