

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
75 X 75 X 30	AD7512LB	BALL	12	0.11	1.32	2200	6.9	0.190	29.0	80	0	CE		
75 X 75 X 30	AD7512MB	BALL	12	0.15	1.80	2600	7.8	0.228	34.9	80	0,3	UL,CUL,CE		
75 X 75 X 30	AD7512HB	BALL	12	0.24	2.88	3000	10.3	0.350	38.5	80	0,2,3	UL,CUL,CE		
75 X 75 X 30	AD7512UB	BALL	12	0.52	6.24	4200	13.1	0.822	44.7	80	0,2,3	CE		
75 X 75 X 30	AD7512MS	S	12	0.20	2.40	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7512HS	S	12	0.30	3.60	3000	10.3	0.350	38.5	80	0,2	UL,CUL,CE		
75 X 75 X 30	AD7524MX	HYPRO	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	CE		
75 X 75 X 30	AD7524HX	HYPRO	24	0.20	4.80	3000	10.3	0.350	38.5	80	0	CE		
75 X 75 X 30	AD7524UX	HYPRO	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
75 X 75 X 30	AD7524MB	BALL	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524HB	BALL	24	0.16	3.84	3000	10.3	0.350	38.5	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524UB	BALL	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
75 X 75 X 30	AD7524LS	S	24	0.12	2.88	2200	6.9	0.190	29.0	80	0	CE		
75 X 75 X 30	AD7524MS	S	24	0.14	3.36	2600	7.8	0.228	34.9	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524HS	S	24	0.16	3.84	3000	10.3	0.350	38.5	80	0	UL,CUL,CE		
75 X 75 X 30	AD7524US	S	24	0.27	6.48	4200	13.1	0.822	44.7	80	0	CE		
80 X 80 X 15	AD0805MX-D71	HYPRO	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0805HX-D71	HYPRO	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0805MB-D71	BALL	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.24
80 X 80 X 15	AD0805HB-D70	BALL	5	0.40	2.00	3200	29.9	0.129	33.4	63	0	CE	200	32.34
80 X 80 X 15	AD0805HB-D71	BALL	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805MS-D71	S	5	0.24	1.20	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805HS-D70	S	5	0.40	2.00	3200	29.9	0.129	33.4	63	0	CE	200	32.34
80 X 80 X 15	AD0805HS-D71	S	5	0.43	2.15	3200	29.9	0.129	31.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LX-D70	HYPRO	12	0.09	1.08	2000	20.0	0.050	19.6	63	0	UL,CUL,TUV,CE	200	32.24
80 X 80 X 15	AD0812MX-D70	HYPRO	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE		
80 X 80 X 15	AD0812MX-D71	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MX-D73	HYPRO	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE		
80 X 80 X 15	AD0812HX-D70	HYPRO	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D71	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D73	HYPRO	12	0.19	2.28	3200	28.0	0.107	28.1	63	3	CE	200	32.34
80 X 80 X 15	AD0812LB-D70	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LB-D73	BALL	12	0.09	1.08	2000	20.0	0.050	19.6	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D70	BALL	12	0.12	1.44	2440	22.4	0.083	26.0	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D71	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MB-D73	BALL	12	0.15	1.80	2440	22.4	0.083	26.0	63	3	CE	200	32.34
80 X 80 X 15	AD0812MB-D74	BALL	12	0.08	0.96	2440	22.1	0.087	25.4	63	4	UL,CUL,CE	200	32.34
80 X 80 X 15	AD0812HB-D70	BALL	12	0.18	2.16	3200	29.9	0.129	33.4	63	0,6	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D71	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	1	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D72	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	2	CE	200	32.34
80 X 80 X 15	AD0812HB-D73	BALL	12	0.19	2.16	3200	29.9	0.129	33.4	63	3	TUV,CE	200	32.34
80 X 80 X 15	AD0812HB-D74	BALL	12	0.17	2.16	3200	29.9	0.129	33.4	63	4	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812LS-D70	S	12	0.09	1.08	2000	20.0	0.050	19.6	63	0,6	UL,CUL,TUV,CE	200	32.34

NOTE B=Ball S=Sleeve X=Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED