


Rev.	Description	Date
G1		


混合式步进电机规格书 HYBRID STEPPING MOTOR SPECIFICATION

外形图 (DIMENSIONS) unit=mm



电气原理图

Wiring Diagram



励磁顺序vs.旋转方向

Exciting Sequence vs. Direction of Rotation

STEP	A	B	C	D	O	M	CCW
1	-	-	-	-	+	+	↑
2	-	-	-	-	+	+	
3	-	-	-	-	+	+	
4	-	-	-	-	+	+	

从安装面看为顺时针方向

Clockwise view from mounting side

No.	Item	Specification	No.	Item	Specification
1	Number of Phase	4	7	Insulation Class	B
2	Step Angle	$1.8^\circ \pm 5\%$	8	Insulation Resistance	$100M \Omega$ (500VDC)
3	Rated Voltage	12V DC	9	Holding Torque	2.0Kg.cm
4	Rated Current	0.4A/Phase			
5	Resistance Per Phase	$30 \Omega \pm 10\%$			
6	Inductance Per Phase	$22mH \pm 20\%$			

Drawn	Bruce	08/23/2021	Unit: mm	
Checked			<h1>Sinotech</h1>	
Eng Appr.				
Mfg Appr.				
Q.A.				
SKU:	2327183		Size :A4	Weight(Kg):
			Scale 1:1	