



Date	Rev.	Description


DIMENSIONS(±0.2mm)



P.C.B LAYOUT
(BOTTOM VIEW)



WIRING DIAGRAM
(BOTTOM VIEW)



CONTACT RATING

1 FORM C (1PDT)	Resistive (Cos.θ = 1)	AC 125V / 1A	DC 24V / 1A
		Max. Switch Current	1A

COIL DATA(0.15W,0.2W, at 25°C)

Coil Nominal Voltage (VDC)	Resistance Tol.±10% (Ohms)		Nominal Current (mA)		Maximum Pick Up Voltage (V)	Minimum Drop Out Voltage (V)
	0.15W	0.2W	0.15W	0.2W		
3	60	45	50.0	66.7	2.4	0.3
5	167	125	30.0	40.0	4.0	0.5
6	240	180	25.0	33.3	4.8	0.6
9	540	405	16.6	22.2	7.2	0.9
12	960	720	12.5	16.7	9.6	1.2
24	3,840	2,880	6.25	8.3	19.2	2.4

GOLDSUN ELECTRONICS CO., LTD.

PART NO. 2333111 Rev. 1

Description :

UNIT mm	SCALE	SHEET 1 OF 1	CAS No: ERN No:
------------	-------	--------------	--------------------

DRAWN : Jay

VERIFY : Arthur / Sam

DCC. NO.

A4 DRAWING NO.