

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 238458

Model	Voltage		No-Load		At Maximum Efficiency					Stall		
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque		Output Power	Torque		Current
			r/min	A	r/min	A	g.cm	mN.m	W	g.cm	mN.m	A
RF-300CA-14270	0.5-4.0	1.9V	3500	0.032	2700	0.12	3.8	0.37	0.11	18	1.76	0.42
RF-300CA-11440	0.7-5.0	2V	2200	0.018	1600	0.055	2.8	0.27	0.057	12	1.18	0.17
RF-300CA-13300	1-6	2V	3300	0.025	2700	0.85	3.0	0.29	0.083	17	1.67	0.35
RF-300CA-11400	1-6	3V	3000	0.018	2400	0.065	4.3	0.42	0.11	21	2.06	0.28
RF-300CA-12400	1-6	3V	4000	0.022	3000	0.090	5.0	0.49	0.15	23	2.26	0.33
RF-300CH-11400	1-6	3V	3000	0.018	2400	0.65	4.3	0.42	0.11	21	2.06	0.29
RF-300CH-11440	0.7-5.0	2V	2200	0.015	1600	0.055	2.8	2.8	0.057	12	1.18	0.17



Shaft L1: 4.8 mm

