

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 240769

3296 cermet trimmer potentiometer

Electrical characteristics:
 Standard resistance range: 10(Ohms) -2M(Ohms)
 Resistance tolerance: $\pm 5\%$, $\pm 10\%$
 Terminal resistance: $\leq 1\%R$ or 2(Ohms)
 Contact resistance variation: $\leq 3\%R$ or 3(Ohms)
 Environment characteristics:
 Rated power: $+70^{\circ}$ 0.5W, $+125^{\circ}$ 0W
 Temperature range: -55° $+125^{\circ}$
 Physical characteristics:
 Total mechanical travel: 30 ± 2 cycles
 Starting torque: ≤ 36 mN.m
 Clutch torque: ≤ 36 mN.m
 Standard packaging: 50pcs/tube

Model	Resistance (Ω)
3296Y-1-101	100
3296Y-1-102	1,000
3296Y-1-103	10,000
3296Y-1-104	100,000
3296Y-1-105	1,000,000
3296Y-1-200	20
3296Y-1-201	200
3296Y-1-202	2,000
3296Y-1-203	20,000
3296Y-1-205	2,000,000
3296Y-1-253	25,000
3296Y-1-500	50
3296Y-1-501	500
3296Y-1-502	5,000
3296Y-1-503	50,000
3296Y-1-504	500,000

