


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 254036



Series	P/N	MFG	Resistance (Ohms)	Characteristics							
				Total Mechanical Travel	Withstand Voltage	Effective Electrical Travel	Rated Power	Starting Torque	Insulation Resistance	Standard Packaging	Mechanical Endurance
P	253982	3362P-1-102	1,000	250°±10°	101.3KPa 500V 8.5KPa 315V	210°±10°	+70°C 0.5W +125°C 0W	≤20mN.m	R1 ≥ 1G Ω	50pcs/tube	200 cycles ΔR ≤ ±10%R
	254036	3362P-1-104	100,000								
	254028	3362P-1-503	50,000								
	254044	3362P-1-504	500,000								
W	254175	3362W-1-102	1,000	210°±10°	+70°C 0.5W +125°C 0W	200 cycles ΔR ≤ ±10%R					
	254204	3362W-1-103	10,000								
	254247	3362W-1-104	100,000								