

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 254669

## 3266 cermet trimmer potentiometer

Electrical characteristics:

Standard resistance range: 10(Ohms) - 2M(Ohms)

Resistance tolerance:  $\pm 5\%$ ,  $\pm 10\%$

Terminal resistance:  $\leq 1\%R$  or 2(Ohms)

Contact resistance variation:  $\leq 3\%R$  or 3(Ohms)

Environment characteristics:

Rated power:  $+70^\circ$  0.25W,  $+125^\circ$  0W

Temperature range:  $-55^\circ$   $+125^\circ$

Physical characteristics:

Total mechanical travel:  $14 \pm 2$  cycles

Starting torque:  $\leq 25$  mN.m

Clutch torque:  $\leq 25$  mN.m

Standard packaging: 50 pcs/tube

Model	Resistance( $\Omega$ )
3266W-1-103	10,000
3266W-1-104	100,000
3266W-1-105	1,000,000
3266W-1-201	200
3266W-1-202	2,000
3266W-1-203	20,000
3266W-1-204	200,000
3266W-1-253	25,000
3266W-1-500	50
3266W-1-501	500
3266W-1-502	5,000
3266W-1-503	5,000
3266W-1-504	500,000

