

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 302738

DRAWING MADE IN AMERICAN PROJECTION

LOC

PRINT DIST


G

14/65

© 1957 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
G	REV PER 063A-0770-00	14/Dec/60	JRC/over



FOR .115 TO .170 WIRE INSULATION DIA.
TONGUE MATERIAL THK = .031 ± .002

NOTE:

- 1. STAMPING MAY BE ON TOP OR BOTTOM.
- 2. SUPERSEDED BY 8-320565-1

QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
50	LOOSE PC. BAG	8-320565-5	BODY & SLEEVE: COPPER (QQ-C-576) TIN PL (MIL-T-10727)
100	LOOSE PC. BOX	8-320565-1	
1	320565 ON TAPE	2-320565-1	INSULATION: BLUE NYLON (MIL-M-20693) TYPE I
1	WIRE TERMINAL	320565	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMALS: .008 ANGLES: 1/2

MATERIAL: SEE TABLE

CONTRACT NO. _____

DRN: *JM* 3/11/69

CHK: *15M* 3/20/69

APPD: *Swahel* 4/1/69

REL: *JM* 4/15/69

DSGN APPD: _____

OTHER APPD: _____

AMP AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

NAME: WIRE TERMINAL
P.I.D.G.-RING TONGUE
WIRE SIZE: 16-14

SIZE: A CODE IDENT NO: 00779 NUMBER: 320565

SCALE: NTS SHEET: 1 OF 1