


NEMA 5-15P (MSL-105)

PACKING:



⚠ P1: cULus E210037-VN ⚠ ⚠

⚠ * NOTE: All relevant materials are complied with RoHS directive .
THE CABLE MARKING IS CONCAVE LETTERING MOULD

⚠

MARKING: (UL) SVT 3/C 18AWG(0.824MM²) VW-1 75°C 300V E204978

C(UL) SVT 3/C 0.824MM²(18AWG) FT2 60°C 300V E204978 MSL-VN-

105IB1F18I(FP048-03)			
P1	STRIPPED JACKET 50mm		
BLACK	L	_____	TINNED 5mm
WHITE	N	_____	TINNED 5mm
GREEN	E	_____	TINNED 5mm

營一部
 2020.10.28
 陳克璋

2	UL SVT 18AWGx3C, OD6.3mm, JACKET GREY(A8344),DRAWING No.EPSVT011803C-099	H5TB10-0304K09	1830mm	M304	
1	MOLDED PVC 35P, JACKET GREY(B8344)	H1BC02-0304G09		M304	
	BRACKET: YS-002	A1QC07-0767W09	1	M767	
	TERMINAL: 98661BS-1	A1QB01-0257	2	M257	
	TERMINAL: Ø4.75, 98475BS-1	A1QB06-0257	1	M257	
No.	DESCRIPTION			Q'TY	Supplier

APPROVED	
CHECKED	HU
DESIGNER	JIANG
DRAWING	YU
DATE	28/OCT/20



COMTOP
CONNECTIVITY SOLUTIONS INC.

15181 Fairfield Ranch Road #100, Chino Hills, CA 91709
Tel.: (909) 597-0883, Fax: (909) 597-0939

Cable Length Unless Other Spec.	
Tolerances:	
0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm ↑	±40mm

⚠ REV.3 2020.10.28	MODIFY MARKING		
⚠ REV.1 2015.08.20	MODIFY MODEL LOGO	⚠ REV.2 2018.05.09	MODIFY MODEL LOGO & CABLE
NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT ±25mm; Another ±50mm			

DATE	28/OCT/20	ITEM NO.	M709-41	UNIT:mm	
------	-----------	----------	---------	---------	--