

Distributed by:


**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 420224

| REVISIONS |     |             |          |          |
|-----------|-----|-------------|----------|----------|
| ZONE      | REV | DESCRIPTION | DATE     | APPROVED |
|           | A   | New Release | 08/05/02 | H.T.     |



|         |         |
|---------|---------|
| MSL-106 | MSL-107 |
| N _____ | N _____ |
| E _____ | E _____ |
| L _____ | L _____ |

|  |                              |                                    |     |
|--|------------------------------|------------------------------------|-----|
| <input checked="" type="checkbox"/> SVT              | <input type="checkbox"/> SJT | <input type="checkbox"/> SJTW      | AWG |
|  |                              |                                    | 18  |
| UL/CSA:60°C  |                              |                                    |     |
| UL/CSA:60°C SHIELDED                                 |                              |                                    |     |
| <input checked="" type="checkbox"/> UL/CSA:60°C~75°C |                              |                                    |     |
| UL/CSA:60°C~75°C SHIELDED                            |                              |                                    |     |
| UL/CSA:105°C   |                              |                                    |     |
| UL/CSA:105°C SHIELDED                                |                              |                                    |     |
| <input type="checkbox"/> NON MIGRATION               |                              | <input type="checkbox"/> MIGRATION |     |

| PART NO.   | CABLE LENGTH |
|------------|--------------|
| 10W1-02206 | 6 ft.        |

**SPECIFICATION:**

- (1).LENGTH: 6FT
- (2).JACKET COLOR: BLACK  
INSULATION COLOR: (BLACK) (WHITE) (GREEN)
- (3).MALE: MSL-106 (A) 10 (V) 125  
APPROVAL: UL CSA
- (4).FEMALE: MSL-107 (A) 10 (V) 125  
APPROVAL: UL CSA
- (5).CABLE: SVT 18AWG\*3C 75°C

**(6).NOTES:**

- 1.MALE: MSL-106  
APPROVAL: E210037
- 2.FEMALE: MSL-107  
APPROVAL: E210037



**NOTE: ALL RELEVANT MATERIALS ARE COMPLIED WITH ROHS DIRECTIVE**

|  |  |   |
|--|--|---|
| <small>UNLESS OTHERWISE SPECIFIED:<br/>1. DIMENSIONS ARE IN MM<br/>2. TOLERANCES DECIMALS X.XX .025<br/>3. DO NOT SCALE DRAWING<br/>4. REMOVE ALL BURRS AND<br/>SHARP EDGES<br/>PROPRIETARY DOCUMENT<br/>THIS DRAWING AND/OR INFORMATION IS<br/>SUBJECT MATTER COVERED UNDER<br/>PATENT NOT BE USED, COPIED OR<br/>DISSEMINATED IN ANY MANNER, OR FOR<br/>ANY PURPOSE, OTHER THAN AS<br/>EXPRESSLY STATED BY<br/>COMTOP ENTERPRISE CORP.</small> | CUSTOMER   | 268 Benton Ct.<br>Industry, CA 91789<br>Tel: 909-458-9737, Fax: 909-458-3728  |
|  | CUSTOMER APPROVAL                                |   |
|  | DRAWN: Howie Tamng<br>DATE: 08/05/02<br>CHECKED: | TITLE: Monitor Power Cord Extension<br>SIZE: 10W1-022<br>P/CSM NO.: 10W1-022<br>DWG NO.: 10W1-022<br>SCALE: NONE<br>Release Date: 08/05/02<br>SHEET: 1 OF 1 |
|  | REV: A   |   |