






OLD ITEM NUMBER : 8200 Series

REV	ECN NO.	DATE
A		



▽ DIP2 PITCH 2.54MMX7.62MM I.D.C. DIP PLUG

FOR PITCH 1.27MM CENTER FLAT RIBBON CABLE



- MATERIAL & FINISH**
 *INSULATOR:PBT+GLASS FIBER UL 94V-0
 *CONTACT:BRASS
 *FINISH: GOLD-PLATED OVER NICKEL
- SPECIFICATIONS**
 *CURRENT RATING: 1A AC,DC
 *VOLTAGE RATING: 250V AC,DC
 *TEMPERATURE RANGE: -40°C TD +105°C
 *CONTACT RESISTANCE: 20MΩ MAX
 *INSULATION RESISTANCE: 1,000MΩ MIN
 *WITHSTANDING VOLTAGE: 500V AC/MIN

2026-254-13-XX

PART NO	DIM A	DIM B	PART NO	DIM A	DIM B
DIP2-08	7.62	15.42	DIP2-24	27.94	35.74
DIP2-10	10.16	17.96	DIP2-26	30.48	38.28
DIP2-14	15.24	23.04	DIP2-28	33.02	40.82
DIP2-16	17.78	25.58	DIP2-34	40.64	48.44
DIP2-18	20.32	28.12	DIP2-40	48.26	56.06
DIP2-20	22.86	30.66			

DIMENSIONS:MM

SIGNATURE		DATE		TITLE: IDC DIP PLUG		CODE NO.		TOLERANCE:		Top Willing Co., Ltd.	
DRN. 邱平		2002/04/25		PITCH2.54mm*7.62mm		CUS. NO.		XX.		DRAWING NO.	
CHK.				C.Y. P/N:		SCALE		X. ±0.2		DIP0.1" *0.3	
APP.				CUS. P/N:		UNIT		XX ±0.10		DIP0.1" *0.3	
						PAGE		ANG.			
						1					

A B C D E F G H I J K L M N O P Q R S T U

0 1 2 3 4 5 6 7 8 9 10