


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 503521



Material: Copper



Wire Range AWG	Stud Size S	Max. Width W	Min. Clearance C	Krimptite®			Insulkrimp® (PVC Insulation)		
				Loose Piece Order No.	Mylar Tape Order No.	Max. Length L	Loose Piece Order No.	Mylar Tape Order No.	Max. Length L
24-26 (0.20-0.12)	0 (1.5)	3.80 (.150)	3.10 (.121)	19069-0369	19069-0407	9.30 (.366)			
	2 (2)	3.80 (.150)	3.10 (.121)	19069-0370	19069-0371	9.30 (.366)			
		5.40 (.213)	5.50 (.215)	19069-0352	19069-0353	12.50 (.492)			
		3.80 (.150)	5.50 (.215)	19069-0358	19069-0405	11.70 (.460)			
	4 (2.6)	5.40 (.213)	5.50 (.215)	19069-0354	19069-0355	12.50 (.492)			
		5.40 (.213)	5.50 (.215)	19069-0356	19069-0357	12.50 (.492)			
	6 (3.5)	6.60 (.260)	7.40 (.290)	19069-0361	19069-0362	15.00 (.590)			
6.60 (.260)		7.40 (.290)	19069-0363	19069-0364	15.00 (.590)				
10 (-)	6.60 (.260)	7.40 (.290)	19069-0365	19069-0406	15.00 (.590)				
18-22 (0.80-0.35)	1-2 (2)	6.00 (.235)	3.90 (.157)	19069-0027	19069-0028	12.30 (.484)	19070-0005	19070-0006	18.00 (.709)
		5.00 (.197)	4.40 (.173)	19069-0025	19069-0026	12.40 (.490)			
	3-4 (2.6)	6.00 (.235)	3.90 (.157)	19069-0029	19069-0030	12.30 (.484)	19070-0007	19070-0008	18.00 (.709)
		6.70 (.264)	6.10 (.240)	19069-0052	19069-0053	14.80 (.582)	19070-0038	19070-0039	20.50 (.807)
		6.00 (.235)	3.90 (.157)	19069-0031	19069-0032	12.30 (.484)	19070-0009	19070-0010	18.00 (.709)
	5-6 (3-3.5)	6.70 (.264)	6.10 (.240)	19069-0054	19069-0055	14.80 (.582)	19070-0040	19070-0042	20.50 (.807)
		8.20 (.322)	7.60 (.300)	19069-0033	19069-0034	17.00 (.671)	19070-0011	19070-0012	22.80 (.896)
	8 (4)	6.70 (.264)	6.10 (.240)	19069-0056	19069-0057	14.80 (.582)	19070-0044	19070-0045	20.50 (.807)
		8.20 (.322)	7.60 (.300)	19069-0035	19069-0036	17.00 (.671)	19070-0013	19070-0014	22.80 (.896)
	10 (-)	7.20 (.283)	6.10 (.240)	19069-0061	19069-0062	15.00 (.591)	19070-0051	19070-0052	20.70 (.816)
		8.20 (.322)	7.60 (.300)	19069-0037	19069-0038	17.00 (.671)	19070-0015	19070-0017	22.80 (.896)
		12.10 (.477)	9.80 (.386)				19070-0021	19070-0022	26.90 (1.060)
	1/4 (6)	12.10 (.477)	9.80 (.386)	19069-0042	19069-0044	21.20 (.835)	19070-0023	19070-0024	26.90 (1.060)
	5/16 (8)	12.10 (.477)	9.80 (.386)	19069-0045	19069-0046	21.20 (.835)	19070-0026	19070-0027	26.90 (1.060)
	3/8 (9)	13.80 (.544)	14.00 (.552)	19069-0049	19069-0050	26.30 (1.034)	19070-0033	19070-0035	31.90 (1.259)
14-16 (2.00-1.30)	1-2 (2)	6.60 (.260)	5.30 (.209)				19070-0065	19070-0066	19.90 (.785)
		6.00 (.260)	5.30 (.209)	19069-0099	19069-0100	14.20 (.560)	19070-0067	19070-0068	19.90 (.785)
	3-4 (2.6)	6.60 (.260)	5.30 (.209)	19069-0101	19069-0102	14.20 (.560)	19070-0069	19070-0070	19.90 (.785)
		8.20 (.322)	7.00 (.275)	19069-0112	19069-0113	16.30 (.640)	19070-0083	19070-0084	22.00 (.865)
	5-6 (3-3.5)	6.60 (.260)	5.30 (.209)	19069-0103	19069-0104	14.20 (.560)	19070-0071	19070-0072	19.90 (.785)
		8.20 (.322)	7.00 (.275)	19069-0114	19069-0115	16.30 (.640)	19070-0086	19070-0087	22.00 (.865)
		8.90 (.352)	7.90 (.310)	19069-0121	19069-0122	17.70 (.696)	19070-0099	19070-0100	23.40 (.921)
	8 (4)	8.20 (.322)	7.00 (.275)	19069-0116	19069-0117	16.30 (.640)	19070-0090	19070-0092	22.00 (.865)
		8.90 (.352)	7.90 (.310)	19069-0123	19069-0124	17.70 (.696)	19070-0102	19070-0104	23.40 (.921)
		12.10 (.477)	9.90 (.388)	19069-0105	19069-0106	21.20 (.837)	19070-0073	19070-0074	26.10 (1.062)
	10 (-)	12.10 (.477)	9.90 (.388)	19069-0107	19069-0108	21.20 (.837)	19070-0075	19070-0076	26.10 (1.062)
		12.10 (.477)	9.90 (.388)	19069-0109	19069-0110	21.20 (.837)	19070-0078	19070-0079	26.10 (1.062)
	1/4 (6)	13.80 (.544)	13.60 (.535)	19069-0096	19069-0097	25.70 (1.010)	19070-0063	19070-0064	31.40 (1.235)
	5/16 (8)	13.80 (.544)	13.60 (.535)	19069-0093	19069-0094	25.70 (1.010)	19070-0059	19070-0061	31.40 (1.235)
		13.80 (.544)	13.60 (.535)						
14-16 (2.00-1.30) Heavy Duty (Also suitable for 12 AWG)	5-6 (3-3.5)	9.80 (.385)	7.70 (.303)				19054-0090	19054-0091	27.30 (1.076)
		9.80 (.385)	7.70 (.303)				19054-0092	19054-0093	27.30 (1.076)
	8 (4)	9.80 (.385)	7.70 (.303)	19044-0163	19044-0164	19.90 (.785)	19054-0094	19054-0095	27.30 (1.076)
		13.70 (.540)	10.00 (.393)				19054-0096	19054-0021	31.60 (1.243)
	10 (-)	13.70 (.540)	10.00 (.393)	19044-0167	19044-0023	24.20 (.952)	19054-0097		31.60 (1.243)
		13.70 (.540)	10.00 (.393)	19044-0168	19044-0024	24.20 (.952)	19054-0098	19054-0099	31.60 (1.243)
	1/4 (6)	15.20 (.598)	11.80 (.466)	19044-0184	19044-0187	26.80 (1.056)			
		15.20 (.598)	11.80 (.466)	19044-0184	19044-0185	26.80 (1.056)	19054-0126	19054-0127	34.20 (1.347)
	5/16 (8)	19.30 (.760)	15.50 (.611)	19044-0140		32.50 (1.280)	19054-0066	19054-0068	39.90 (1.571)
		19.30 (.760)	15.50 (.611)	19044-0142		32.50 (1.280)	19054-0070	19054-0071	39.90 (1.571)
3/8 (9)	19.30 (.760)	15.50 (.611)							
7/16 (11)	19.30 (.760)	15.50 (.611)	19044-0137	19044-0138	32.50 (1.280)	19054-0063		39.90 (1.571)	
	19.30 (.760)	15.50 (.611)							
1/2 (12)	19.30 (.760)	15.50 (.611)							