

Distributed by:

JAMECO[®]
ELECTRONICS


www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.



Jameco Part Number 525333

		REVISIONS				LOC	DIST
P	F	ZONE	LTR	DESCRIPTION	DATE	APP	
		H		REVISED PER EC 051A-0054-99	27AUG99	JG	35

- ① UL RATED 94V-0 THERMOPLASTIC, BLACK.
- ② PHOSPHOR BRONZE PER QQ-B-750.
- ③ .000015 MIN GOLD ON LOCALIZED GOLD PLATE AREA, .000100-.000200 TIN-LEAD ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- ④ POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSITION NUMBER 1 INDICATOR ON 10 AND 14 POSITION PRODUCT.



TERMINATED VIEW



DETAIL Z
SCALE 10:1
TYPICAL

1.125	2.100	2.380	2.150	43	44	1-746285-3
1.625	3.100	3.380	3.150	63	64	1- -2
1.525	2.900	3.180	2.950	59	60	1- -1
1.275	2.400	2.680	2.450	49	50	1- -0
1.025	1.900	2.180	1.950	39	40	-9
.875	1.600	1.880	1.650	33	34	-8
.775	1.400	1.680	1.450	29	30	-7
.675	1.200	1.480	1.250	25	26	-6
.625	1.100	1.380	1.150	23	24	-5
.525	.900	1.180	.950	19	20	-4
.425	.700	.980	.750	15	16	-3
.375	.600	.880	.650	13	14	-2
.275	.400	.680	.450	9	10	746285-1
E	D	C	B	A	NO OF POSN	PART NUMBER

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± 5°	CONTRACT NO	AMP INCORPORATED Harrisburg, Pa.	
	DR J. PEACHEY 9-30-85	NAME	
	CHK W.E. ZELKO 11-21-85	RECEPTACLE KIT, AMP-LATCH NOVO, CTR & MIL PLZN, 15 GOLD DUPLX CONTACTS, W/O STRAIN RLF	
	MATERIAL APPD JAY SAUDER 11-21-85 APPD D. HOFFMAN 11-21-85	SIZE D	FSCM NO 00779
FINISH CONTACTS: ③	OSGN APPD	SCALE 4:1	SHEET 1 of 1