

Distributed by:

JAMECO[®]
ELECTRONICS




www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 526061

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AR	35				F	REDRAWN	2-23-90	-
					G	OBS -15 PER EC 0020-0141-94	04/04/94	JS
					H	REV PER 051A-0008-00	03/31/00	CR



OBSOLETE	1.990	1.834	36	1-499252-5
OBSOLETE	1.290	1.134	22	1-499252-4
	3.390	3.234	64	1-499252-3
	1.690	1.534	30	1-499252-2
	2.390	2.234	44	1-499252-1
	1.390	1.234	24	1-499252-0
	.890	.734	14	499252-9
	.990	.834	16	499252-8
	3.190	3.034	60	499252-7
	1.890	1.734	34	499252-6
	.690	.534	10	499252-5
	2.690	2.534	50	499252-4
	1.490	1.334	26	499252-3
	1.190	1.034	20	499252-2
	2.190	2.034	40	499252-1
	B	A	NO OF POSN	PART NUMBER

- 1 MATERIAL: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK.
- 2 AMP TRADEMARK AND MOLD CAVITY LETTER TO BE MOLDED ON THIS SURFACE.
- 3 ALTERNATE LOCATION FOR AMP TRADEMARK AND CAVITY ID.
- 4 CORING SLOTS IN BOTH SIDES AS INDICATED, OR IN UNDERSIDE OF PART.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -		DR 2-23-90 J GALLUCCI BG		AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL 1		CHK 3-5-90 H.MOLL			
FINISH -		APPD 3-6-90 S.GOOD		NAME	
		APPD 3-6-90 D.HOFFMAN		STRAIN RELIEF, RECEPTACLE CONNECTOR, FLAT CABLE, AMP-LATCH™	
		PRODUCT SPEC -		SIZE C	
		APPLICATION SPEC -		FSCM NO 00779	
		WEIGHT -		DRAWING NO 499252	
				SCALE 10:1	
				SHEET 1 OF 1	