

| Date | Rev. | Description |
|------|------|-------------|
|      |      |             |
|      |      |             |
|      |      |             |

# L01 1.27mm FLAT RIBBON CABLE


UL File No. : E162690  
 UL Style : 2651  
 Operating Temperature : -20°C to +105°C  
 Flammability Rating : UL-VW-1  
 Voltage Rating : 300V

**Physical**

Insulation Material : Polyvinyl Chloride (PVC)  
 Conductor : #28AWG (7\*0.127) Stranded Tinned Copper  
                   #26AWG (7\*0.16) Stranded Tinned Copper  
 Color : Grey With Red Edge

**Electrical**

Impedance : 115Ω (Unbalanced)  
 Capacitance : 12.2 pF/ft.  
 Inductance : .14μH/ft.  
 Propagation Delay : 1.4 ns/ft.  
 Insulation Resistance : 1GΩ/M min.



**HOW TO ORDER:**

L01 -  -  -  -  UNIT - G (RoHS)

|                                |                                 |                                       |  |
|--------------------------------|---------------------------------|---------------------------------------|--|
| 1.NO. OF CONDUCTOR<br>06 TO 64 | 2.INSULATION MATERIAL<br>P: PVC | 3.WIRE SIZE<br>A: 28 AWG<br>B: 26 AWG | 4.CABLE LENGTH / UNIT<br>C: CM<br>F: FEET<br>I: INCH<br>M: METER |
|--------------------------------|---------------------------------|---------------------------------------|--|

|                |
|----------------|
| DCC. NO.       |
| A4 DRAWING NO. |

|                                    |                                      |        |                    |
|------------------------------------|--------------------------------------|--------|--------------------|
| MATERIAL                           | <b>GOLDSUN ELECTRONICS CO., LTD.</b> |        |                    |
| JAMECO NO.<br><b>644130</b>        |                                      |        |                    |
| DRAWN: Kiki Chen                   | Description<br>CABLE RIBBON          |        | Rev.<br>1          |
| VERIFY PEOPLE: Ada Zheng , Ivy Lan | UNIT:<br>mm                          | SCALE: | CAS No:<br>ERN No: |
|                                    | SHEET 1 OF 1                         |        |                    |