



Consolidated

ELECTRONIC WIRE & CABLE

24 and 22 AWG Wire 2 to 60 Conductor Data Grade Multi Conductor Foil Shielded Consolidated Computer Cable (UL) CM/GMG or CMG UL Style 2464 c(UL) or C(UL)us

Product Construction

Conductor:

- 24 thru 22 AWG annealed tinned copper wire per ASTM B-33

Insulation:

- Color coded semi rigid PVC per UL 1061

Shield:

- 100% coverage Polyester/Aluminum foil.
- Stranded tinned copper drain wire
- Cable shielded

Jacket:

- Chrome gray PVC jacket
- Temperature: -20°C to +80°C (UL)
- Temperature: -20°C to +75°C (CM)
- Voltage: 300 volts



1

<u>Part #</u>	<u>Conductor Size</u>	<u>Strands</u>	<u>No. of Conductors</u>	<u>Insulation Thickness</u>	<u>Foil Shield</u>	<u>Jacket Thickness</u>	<u>Nominal O.D.</u>
<u>5710-CL</u>	24 AWG	7 x 32 Tin Copper Wire	2	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.160 in.
<u>5711-CL</u>	24 AWG	7 x 32 Tin Copper Wire	3	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.172 in.
<u>5801-CL</u>	24 AWG	7 x 32 Tin Copper Wire	4	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.180 in.
<u>5713-CL</u>	24 AWG	7 x 32 Tin Copper Wire	5	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.190 in.
<u>5714-CL</u>	24 AWG	7 x 32 Tin Copper	6	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned	0.035 in.	0.205 in.

<u>Part #</u>	<u>Conductor Size</u>	<u>Strands</u>	<u>No. of Conductors</u>	<u>Insulation Thickness</u>	<u>Foil Shield</u>	<u>Jacket Thickness</u>	<u>Nominal O.D.</u>
		Wire			copper drain wire		
<u>5715-CL</u>	24 AWG	7 x 32 Tin Copper Wire	7	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.208 in.
<u>5716-CL</u>	24 AWG	7 x 32 Tin Copper Wire	8	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.220 in.
<u>5717-CL</u>	24 AWG	7 x 32 Tin Copper Wire	9	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.240 in.
<u>5718-CL</u>	24 AWG	7 x 32 Tin Copper Wire	10	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.250 in.
<u>5718/12-CL</u>	24 AWG	7 x 32 Tin Copper Wire	12	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.260 in.
<u>5719-CL</u>	24 AWG	7 x 32 Tin Copper Wire	15	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.280 in.
<u>5720/18-CL</u>	24 AWG	7 x 32 Tin Copper Wire	18	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.290 in.
<u>5720-CL</u>	24 AWG	7 x 32 Tin Copper Wire	20	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.310 in.
<u>5725-CL</u>	24 AWG	7 x 32 Tin Copper Wire	25	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.370 in.
<u>5730-CL</u>	24 AWG	7 x 32 Tin Copper Wire	30	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.390 in.
<u>5740-CL</u>	24 AWG	7 x 32 Tin Copper Wire	40	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.440 in.
<u>5750-CL</u>	24 AWG	7 x 32 Tin Copper Wire	50	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.450 in.
<u>5722-CL</u>	22 AWG	7 x 30 Tin Copper Wire	2	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.170 in.
<u>5723-CL</u>	22 AWG	7 x 30 Tin Copper Wire	3	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.177 in.

<u>Part #</u>	<u>Conductor Size</u>	<u>Strands</u>	<u>No. of Conductors</u>	<u>Insulation Thickness</u>	<u>Foil Shield</u>	<u>Jacket Thickness</u>	<u>Nominal O.D.</u>
<u>5724-CL</u>	22 AWG	7 x 30 Tin Copper Wire	4	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.200 in.
<u>5731-CL</u>	22 AWG	7 x 30 Tin Copper Wire	5	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.210 in.
<u>5726-CL</u>	22 AWG	7 x 30 Tin Copper Wire	6	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.226 in.
<u>5727-CL</u>	22 AWG	7 x 30 Tin Copper Wire	7	0.010 in.	Polyester/Aluminum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.230 in.
<u>5728-CL</u>	22 AWG	7 x 30 Tin Copper Wire	8	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.240 in.
<u>5729-CL</u>	22 AWG	7 x 30 Tin Copper Wire	9	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.258 in.
<u>5732-CL</u>	22 AWG	7 x 30 Tin Copper Wire	10	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.275 in.
<u>5735-CL</u>	22 AWG	7 x 30 Tin Copper Wire	15	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.308 in.
<u>5735/18-CL</u>	22 AWG	7 x 30 Tin Copper Wire	18	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.320 in.
<u>5736-CL</u>	22 AWG	7 x 30 Tin Copper Wire	20	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.035 in.	0.340 in.
<u>5737-CL</u>	22 AWG	7 x 30 Tin Copper Wire	25	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.370 in.
<u>5738-CL</u>	22 AWG	7 x 30 Tin Copper Wire	30	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.420 in.
<u>5739-CL</u>	22 AWG	7 x 30 Tin Copper Wire	40	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.040 in.	0.465 in.
<u>5741-CL</u>	22 AWG	7 x 30 Tin Copper Wire	50	0.010 in.	Polyester/Alum foil shield, 25% overlap and stranded tinned copper drain wire	0.045 in.	0.505 in.

Consolidated Electronic Wire & Cable - 11044 King St., Franklin Park, Illinois 60131 | Toll Free: 800-621-4278 • Phone: 847-455-8830 • Fax: 847-455-8837 | Email: info@conwire.com