



Multi-Conductors UL2464 with Foil Shield 24 AWG

Consolidated
ELECTRONIC WIRE & CABLE

Product Details:

- Annealed Stranded Tin Copper Conductor
- 100% Aluminum Foil Coverage with 25% Overlap with Annealed Stranded Tin Copper (ASTM B-33) Drain Wire
- Semi-rigid PVC Insulation Thickness .010" with Gray PVC Jacket 300V
- CM/CMG Rated -20C to 75C, UL2464 Rated -20C to 80C
- Approvals: CM/CMG, UL2464, VW-1, ROHS Compliant

Consolidated Electronic Wire & Cable

11044 King St.
Franklin Park, Illinois 60131

800-621-4278

www.conwire.com

Part Number	Construction	C/PR	Insulation	Jacket Material	Jacket Thickness	Nom. OD (in)	Style	Color Code
5710-CL	24 (7x32) TC	2C	PVC	PVC	0.035	0.16	CM / UL 2464	<u>1</u>
5711-CL	24 (7x32) TC	3C	PVC	PVC	0.035	0.163	CM / UL 2464	<u>1</u>
5801-CL	24 (7x32) TC	4C	PVC	PVC	0.035	0.18	CM / UL 2464	<u>1</u>
5713-CL	24 (7x32) TC	5C	PVC	PVC	0.035	0.19	CM / UL 2464	<u>1</u>
5714-CL	24 (7x32) TC	6C	PVC	PVC	0.035	0.205	CM / UL 2464	<u>1</u>
5715-CL	24 (7x32) TC	7C	PVC	PVC	0.035	0.205	CM / UL 2464	<u>1</u>
5716-CL	24 (7x32) TC	8C	PVC	PVC	0.035	0.219	CM / UL 2464	<u>1</u>
5717-CL	24 (7x32) TC	9C	PVC	PVC	0.035	0.232	CM / UL 2464	<u>1</u>
5718-CL	24 (7x32) TC	10C	PVC	PVC	0.035	0.25	CM / UL 2464	<u>1</u>
5718/12-CL	24 (7x32) TC	12C	PVC	PVC	0.035	0.256	CM / UL 2464	<u>1</u>
5719-CL	24 (7x32) TC	15C	PVC	PVC	0.035	0.272	CM / UL 2464	<u>2</u>
5720/18-CL	24 (7x32) TC	18C	PVC	PVC	0.035	0.29	CM / UL 2464	<u>2</u>
5720-CL	24 (7x32) TC	20C	PVC	PVC	0.035	0.3	CM / UL 2464	<u>2</u>
5725-CL	24 (7x32) TC	25C	PVC	PVC	0.035	0.337	CM / UL 2464	<u>2</u>
5730-CL	24 (7x32) TC	30C	PVC	PVC	0.035	0.39	CM / UL 2464	<u>2</u>
5740-CL	24 (7x32) TC	40C	PVC	PVC	0.035	0.44	CM / UL 2464	<u>2</u>
5750-CL	24 (7x32) TC	50C	PVC	PVC	0.035	0.45	CM / UL 2464	<u>2</u>

Consolidated Color Code Chart #1 - Conductors

No. Of Cond.	Color	No. Of Cond.	Color	No. Of Cond.	Color
1	Black	2	Red	3	Green
4	White	5	Brown	6	Blue
7	Orange	8	Yellow	9	Purple
10	Slate	11	Pink	12	Tan

Consolidated Color Code Chart #2 - Conductors

No. Of Cond.	Color	No. Of Cond.	Color	No. Of Cond.	Color
1	Black	2	White	3	Red
4	Green	5	Orange	6	Blue
7	White/Black	8	Red/Black	9	Green/Black
10	Orange/Black	11	Blue/Black	12	Black/White
13	Red/White	14	Green/White	15	Blue/White
16	Black/Red	17	White/Red	18	Orange/Red
19	Blue/Red	20	Red/Green	21	Orange/Green
22	Black/White/Red	23	White/Black/Red	24	Red/Black/White
25	Green/Black/White	26	Orange/Black/White	27	Blue/Black/White
28	Black/Red/Green	29	White/Red/Green	30	Red/Black/Green
31	Green/Black/Orange	32	Orange/Black/Green	33	Blue/White/Orange
34	Black/White/Orange	35	White/Red/Orange	36	Orange/White/Blue
37	Orange/White/Blue	38	Black/White/Green	39	White/Black/Green
40	Red/White/Green	41	Green/White/Blue	42	Orange/Red/Green
43	Blue/Red/Green	44	Black/White/Blue	45	White/Black/Blue
46	Red/White/Blue	47	Green/Orange/Red	48	Orange/Red/Blue
49	Blue/Red/Orange	50	Black/Orange/Red	51	White/Black/Orange
52	Red/Orange/Black	53	Green/Red/Blue	54	Orange/Black/Blue
55	Blue/Black/Orange	56	Black/Orange/Green	57	White/Orange/Green
58	Red/Orange/Green	59	Green/Black/Blue	60	Orange/Green/Blue

Note: All specifications are subjected to change without prior notice.