



PIN ASSIGNMENT			
P1		P2	
1	—————	1	RED 24#
2	———X———	2	WHITE
3	———X———	3	GREEN
4	—————	5	BLACK 24#
SHIELD	—————	SHIELD	

NOTE: All relevant materials are complied with RoHS directive .

No.	DESCRIPTION	Q'TY	Supplier
5	BLACK HEAT SHRINK TUBE $\phi 1.0 \times 5\text{mm}$	4	M743
	MOLDED PVC BLACK		M304
4	MOLDED PVC BLACK		M304
3	USB 2.0 CABLE, UL STYLE 1 TWISD PAIR 28AWG AND 2C 24AWG,OD 4.5mm, AMA BRAID, JACKET BLACK, DRAWING No. EUAB2801P2402C-139	1810mm	M304
2	MINI USB 5P MALE 2.0, GOLD PLATING 30 $\mu$ " ON CONTACTS, BLACK INSULATOR	1	M108
1	USB A MALE 2.0, GOLD PLATING 30 $\mu$ " ON CONTACTS, WHITE INSULATOR, SHORT A PIERCE TYPE	1	M108

APPROVED		<p><b>COMTOP</b> Enterprises Corp. 268 Benton Court City of Industry, CA 91789 Tel: (909) 468-5737 Fax: (909) 468-5726</p>	<p>Cable Length Unless Other Spec. Tolerances:</p> <table border="0"> <tr> <td>0 ~200mm</td> <td>±10mm</td> </tr> <tr> <td>201 ~1000mm</td> <td>±20mm</td> </tr> <tr> <td>1001 ~1500mm</td> <td>±25mm</td> </tr> <tr> <td>1501 ~2100mm</td> <td>±30mm</td> </tr> <tr> <td>2100mm↑</td> <td>±40mm</td> </tr> </table>	0 ~200mm	±10mm	201 ~1000mm	±20mm	1001 ~1500mm	±25mm	1501 ~2100mm	±30mm	2100mm↑	±40mm
0 ~200mm	±10mm												
201 ~1000mm	±20mm												
1001 ~1500mm	±25mm												
1501 ~2100mm	±30mm												
2100mm↑	±40mm												
CHECKED	HU												
DRAWING	LI												
DATE	12/DEC/08	ITEM NO.	10U2-15106										
CHECKED		UNIT:mm											