


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 697493



0.500" x 0.250" 0.350" x 0.150" 0.750" x 0.150"
LED LIGHT BARS
 UNIVERSAL SIZE - LARGE UNIFORM LIGHT AREAS

LED USED	LED RADIATION COLOR	ELECTRO-OPTICAL CHARACTERISTICS Ta=25°C Ir=100µA(MAX)				LIGHTED AREA IN INCHES & mm	CROSS REFERENCE	FIG.
		If mA	Iv min/typ	Vf typ/max	λP nm			
LTL-57173HR	HI-EFF. RED	10	3.8/9.8	2.1/2.8	635	0.500" x 0.250" 12.7mm x 6.35mm	MVS57173	A
LTL-53173Y	YELLOW	10	3.2/9.0	2.1/2.8	585		MVS54173	
LTL-54173G	GREEN	10	3.8/9.8	2.1/2.8	565		MVS53173	
LTL-2300HR	HI-EFF. RED	10	3.2/9.0	2.1/2.8	635	0.350" x 0.150" 8.89mm x 3.81mm	HLMP2300	B
LTL-2400Y	YELLOW	10	2.8/8.2	2.1/2.8	585		HLMP2400	
LTL-2500G	GREEN	10	3.2/9.0	2.1/2.8	565		HLMP2500	
LTL-2350HR	HI-EFF. RED	10	7.0/17.0	2.1/2.8	635	0.750" x 0.150" 14.05mm x 3.81mm	HLMP2350	C
LTL-2450Y	YELLOW	10	6.0/15.0	2.1/2.8	585		HLMP2450	
LTL-2550G	GREEN	10	7.0/17.0	2.1/2.8	565		HLMP2550	
LTL-2655HR	HI-EFF. RED	10	7.0/17.0	2.1/2.8	635	0.35" x 0.35" 8.89mm x 8.89mm	HLMP2655	D
LTL-2755Y	YELLOW	10	6.0/15.0	2.1/2.8	585		HLMP2755	
LTL-2855G	GREEN	10	7.0/17.0	2.1/2.8	565		HLMP2855	
LTL-2685HR	HI-EFF. RED	10	14.0/34.0	2.1/2.8	635	0.35" x 0.75" 8.89mm x 19.05mm	HLMP2685	E
LTL-2785Y	YELLOW	10	12.0/30.0	2.1/2.8	585		HLMP2785	
LTL-2885G	GREEN	10	14.0/34.0	2.1/2.8	565		HLMP2885	
LTL-2600HR	HI-EFF. RED	10	3.2/9.0	2.1/2.8	635	0.35" x 0.150" TWIN 8.89mm x 3.81mm	HLMP2600	F
LTL-2700Y	YELLOW	10	2.8/8.2	2.1/2.8	585		HLMP2700	
LTL-2800G	GREEN	10	3.2/9.0	2.1/2.8	565		HLMP2800	

- FEATURES:**
- * RECTANGULAR LIGHT BAR WITH UNIFORM LIGHT EMITTING AREAS.
 - * CHOICE OF COLORS: HI-EFF RED/GREEN/YELLOW
 - * EXCELLENT ON-OFF CONTRAST
 - * EASILY MOUNTS ON PC BOARDS, STANDARD DIP/SIP SOCKETS
 - * X-Y STACKABLE, FLUSH MOUNTABLE
 - * I.C. COMPATIBLE, SUITABLE FOR MULTIPLEX OPERATIONS

APPLICATIONS:
 LEGEND ILLUMINATION,
 BACKLIGHTING, BARGRAPHS,
 MESSAGE ANNOUNCIATORS,
 TELECOM INDICATORS

MECHANICAL SPECIFICATIONS:

