



ELECTRICAL CHARACTERISTIC

(1)	CONTACT RESISTANCE: $\leq 20\text{m}\Omega$
(2)	INSULATION RESISTANCE: $\geq 10\text{M}\Omega$
(3)	WITHSTAND VOLTAGE: DC300V
(4)	CURRENT RATING: 5A/DC150V
(5)	OPERATING TEMPERATURE: $-30^{\circ}\text{C} \sim 60^{\circ}\text{C}$

7	SHELL	ABS
6	COPPER PATCH	Cu
5	PLASTIC HANDLE	ABS
4	WASHER	Cu
3	EARTHING PATCH	Cu
2	NUT	Zn
1	BODY	Cu

TOLERANCE	SIGNATURES	DATE
0 - 10 ±0.05	DRAFT: cheng huan	10.01.15
10 - 99 ±0.5	CHECKED:	
100 - 999 ±10.0		
1000 - 9999 ±100.00		
10000 - 99999 ±1000.00		

CIC COMPONENTS IND. CO., LTD.	
-------------------------------	--

REV	PART NO. & SAMPLE NO.	DATE	BY
A	03-035		
B			

APPROVAL:		SCALE	UNIT	REV
		1:1	mm	Ø

TITLE	Binding Post, Medium (Red/Black)
CUSTOMER	