


REV.	ECN. NO.	DESCRIPTION
------	----------	-------------



MATERIAL:

INSULATOR :Hi-temp PBT or PPS, UL 94V-0
 Contact material:phosphor bronze JIS 5210
 Contact Plated :120 μtin over 30 μnickel

SPECIFICATIONS:

Temperature range:-50°C to 105°C
 CURRENT Rating :1 AMP
 Capacitance:1.0 Picofarads (Max)
 Contact resistance:30 Milliohms (Max)
 Insulation Resistance :1000 Megohms (Min)
 Withstanding Voltage: AC 600 Vrms

MIDDLE TYPE:

NO OF CONTACT	A±0.2	B±0.2	C±0.1	D±0.1	E±0.1	F±0.1
20 PPS PBT	15.50	15.50	5.08	5.08	5.08	5.08
28 PPS PBT	18.04	18.04	7.62	7.62	7.62	7.62
32 PPS PBT	20.60	18.04	7.62	10.16	7.62	10.16
44 PPS PBT	23.30	23.30	12.70	12.70	12.70	12.70
52 PPS PBT	25.88	25.88	15.24	15.24	15.24	15.24
68 PPS PBT	31.04	31.04	20.32	20.32	20.32	20.32
84 PPS PBT	36.04	36.04	25.40	25.40	25.40	25.40
68 PBT	31.66	31.66	20.32	20.32	20.32	20.32
84 PBT	36.66	36.66	25.40	25.40	25.40	25.40


THIN TYPE:

NO OF CONTACT	A±0.15	B±0.15	C±0.1	D±0.1	E±0.1	F±0.1
44	23.30	23.30	12.70	12.70	12.70	12.70
68	31.04	31.04	20.32	20.32	20.32	20.32
84	36.04	36.04	25.40	25.40	25.40	25.40

UNIT/mm

圖名 DIP PLCC SOCKET

料號 04AA-**3T1S 日期 2010-01-31
 序號 繪圖 CHENYIXIANG



TOLERANCES (EXCEPT AS NOTED)
 MM 0.0-±0.25 0.00-±0.15
 INCH 0.00-±0.01 0.000-±0.006
 RADIUS ±0.25[0.010]
 HOLE ±0.13[0.005]
 ANGLES ±2°