


Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 739366



## RF Connectors

SMA/QMA

AMP 1054874-1  Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 1054874-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<input type="checkbox"/> <a href="#">General Info</a> <input type="checkbox"/> <a href="#">Sales Info</a> <input type="checkbox"/> <a href="#">Assembly Subcontractors</a>	<input type="checkbox"/> <a href="#">Pricing</a> <input type="checkbox"/> <a href="#">Product Availability</a>	<input type="checkbox"/> <a href="#">Tooling</a>

Searchable Features:	
<b>Brand:</b>	AMP
<b>Government/Industry Qualification:</b>	No
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Process:</b>	Not reviewed for lead free solder process
<b>Product Type:</b>	Adapter
<b>Adapter Type:</b>	Jack-Jack
<b>Body Style:</b>	Straight
<b>Panel Attachment:</b>	Yes
<b>Panel Attachment Method:</b>	Bulkhead
<b>Panel Attachment Style:</b>	Rear Mount
<b>Length (mm [in]):</b>	22.20 [0.874]

Other Properties:	
<b>RoHS/ELV Compliance History:</b>	Always was compliant
<b>Impedance ( ):</b>	50
<b>Center Contact Material:</b>	Beryllium Copper
<b>Center Contact Plating:</b>	Gold over Copper
<b>Frequency:</b>	DC to 18 GHz
<b>Dielectric Material:</b>	TFE Fluorocarbon
<b>Lockwasher Material:</b>	Stainless Steel
<b>O-Ring Material:</b>	EPM
<b>Insulation Resistance (M ):</b>	5,000
<b>Comment:</b>	Hermetically Sealed

- [Home](#)
- [Part Number Search](#)
- [Document Search](#)
- [CAD Model Search](#)
- [Text Search](#)
- [Alternate/Lead Free Part Search](#)
- [Multiple Part Comparison](#)
- [Alphabetical Search](#)
- [Brand Search](#)
- [Industry Product Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Competitor Cross Reference](#)
- [Lead Free Solutions](#)
- [Tool Search](#)
- [Help/Glossary](#)

<b>Body Material:</b>	Stainless Steel
<b>Body Finish:</b>	Gold over Nickel
<b>Center Contact:</b>	With
<b>Retractable Collar:</b>	Without

---

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

# i2 Technologies US, Inc.

## HTML Pages converted to PDF Document

This document contains component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

