

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS




**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 746793

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19  
 © COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
		B		REDRAWN PER ECN 651		
B	✓	B1		REV ECN 1895	4-8-88	SB
✓	✓	C		REV LOC & DIST AD-4171	11-28-89	BF
✓	✓	D		OBS PER 0010-0715-93	JH 7-23-93	JLC
✓	✓	E		REV PER 0010-1105-93	4-14-94	EB/JH
✓	✓	F		REV PER 0010-0403-95	5-17-95	EB/JH
		G		REV PER 0310-0460-97	183UN98	WO



OBSOLETE	3.600	3.500	35	72	3-102536-4	
OBSOLETE	3.500	3.400	34	70	3-	-3
OBSOLETE	3.400	3.300	33	68	3-	-2
OBSOLETE	3.300	3.200	32	66	3-	-1
	3.200	3.100	31	64	3-	-0
OBSOLETE	3.100	3.000	30	62	2-	-9
	3.000	2.900	29	60	2-	-8
OBSOLETE	2.900	2.800	28	58	2-	-7
OBSOLETE	2.800	2.700	27	56	2-	-6
OBSOLETE	2.700	2.600	26	54	2-	-5
OBSOLETE	2.600	2.500	25	52	2-	-4
	2.500	2.400	24	50	2-	-3
OBSOLETE	2.400	2.300	23	48	2-	-2
OBSOLETE	2.300	2.200	22	46	2-	-1
OBSOLETE	2.200	2.100	21	44	2-	-0
OBSOLETE	2.100	2.000	20	42	1-	-9
	2.000	1.900	19	40	1-	-8
OBSOLETE	1.900	1.800	18	38	1-	-7
OBSOLETE	1.800	1.700	17	36	1-	-6
	1.700	1.600	16	34	1-	-5
	1.600	1.500	15	32	1-	-4
	1.500	1.400	14	30	1-	-3
	1.400	1.300	13	28	1-	-2
	1.300	1.200	12	26	1-	-1
	1.200	1.100	11	24	1-	-0
	1.100	1.000	10	22		-9
	1.000	.900	9	20		-8
	.900	.800	8	18		-7
	.800	.700	7	16		-6
	.700	.600	6	14		-5
	.600	.500	5	12		-4
	.500	.400	4	10		-3
	.400	.300	3	8		-2
	.300	.200	2	6		102536-1
	C	B	A	NO OF POSITIONS		PART NO.

1. THIS COVER WILL MATE WITH COVER HALVES 102540, 102541, OR 102537

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ±		CONTRACT NO		AMP   AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL FLAME RETARDANT THERMOPLASTIC, COLOR - BLACK		DR <i>W.G. Lenka</i> 5-13-85		NAME COVER-HALF, LOW PROFILE, MT, AMP MODU, .100 E	
FINISH		CHK <i>BA-Mayer</i> 5-14-85		APPD <i>[Signature]</i> 22 MAY 85	
		APPD <i>[Signature]</i> 6/27/85		DSGN APPD	
		OTHER APPD		SIZE	FSCM NO
				C	00779
				DRAWING NO 102536	
				SCALE	SHEET
				NTS	