


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 747972



- Home
- Part Number Search
- Document Search
- CAD Model Search
- Text Search
- Alternate/Lead Free Part Search
- Multiple Part Comparison
- Alphabetical Search
- Brand Search
- Industry Product Search
- Product Type Search
- Product Family Search
- Competitor Cross Reference
- Lead Free Solutions
- Tool Search
- Help/Glossary

RF Connectors

SMA/QMA

AMP 1050524-1 Active [Active](#)

RoHS Compliant [RoHS Compliant](#)

(Tyco Electronics P/N: 1050524-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<input type="checkbox"/> General Info <input type="checkbox"/> Sales Info <input type="checkbox"/> Assembly Subcontractors	<input type="checkbox"/> Pricing <input type="checkbox"/> Product Availability	<input type="checkbox"/> Tooling

Searchable Features:	
Brand:	AMP
Government/Industry Qualification:	No
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Process:	Not reviewed for lead free solder process
Product Type:	Connector
Gender:	Plug
Terminate To:	Coaxial Cable
Coaxial Cable Termination Type:	Solder
Coaxial Cable Type (RG/U or Mfg.):	402 Semi-Rigid/3.58 [.141]
Body Style:	Straight

Other Properties:	
RoHS/ELV Compliance History:	Always was compliant
Impedance ():	50
Center Contact Material:	Beryllium Copper
Center Contact Plating:	Gold
Frequency:	DC to 18 GHz
Dielectric Material:	PTFE Fluorocarbon
Coupling Nut Material:	Stainless Steel
Coupling Nut Finish:	Gold
Shrink Tubing:	Without
Gasket Material:	Silicone Rubber

Panel Attachment:	No
Length (mm [in]):	11.18 [0.440]
Body Material:	Stainless Steel
Body Finish:	Gold
Center Contact:	With
Retractable Collar:	Without
Safety Wire Holes:	Without

Retaining Ring Material:	Beryllium Copper
Insulation Resistance (M)::	5,000

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)

i2 Technologies US, Inc.

HTML Pages converted to PDF Document

This document contains component information from the manufacturer's website which are not available in a revision controlled document from the manufacturer. To facilitate the addition of these parts into the Electronics Database, we are converting the HTML pages related to that part, from the manufacturer's website into Adobe PDF format. The contents of this document is based on the information provided on the manufacturer's website, therefore the information may have been changed by the manufacturer since this was created.

