



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
03 <sub>2</sub>	SEE ECN 80-0084	G.B. 2/14/80	T.S. 2/19/80
03 <sub>3</sub>	REDRAWN IN CAD PER ECN 88-0678	E.F.H. 1/10/90	KCM

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457, MIL-P-19468, AND FED. SPEC L-P-403	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B196, ALLOY 173	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550

COMPONENT	MATERIAL	FINISH
-----------	----------	--------

CABLE ENTRY DIAMETER MINIMUM	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY R.M.K. DATE 9/3/69	AMP Incorporated	
HOUSING .089	FRAC. DEC. ANGLES ± 1/64 ± .005 ± °	CHECKED BY B.D. DATE 9/8/69	140 Fourth Avenue Waltham, MA 02451-7599	
CONTACT .021	These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	APPROVED BY G.B. DATE 9/8/69	AMP	
		USE ASS'Y PROCEDURE	TITLE OSM STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT	
		408-04833 NO. AP. (20-010)	SIZE B	CODE IDENT NO. 26805
			SCALE 5:1	2002-5016-00
				REV 03 <sub>3</sub>
				SHEET 1 OF 1

- NOTES:
- DESIGNED FOR USE WITH .085 DIA SEMI-RIGID CABLE
  - CAPTURED CENTER CONTACT