

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242




The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 751226

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
CM	00	F	REV PER ECN 0G3B-0324-03	11JUN03	SC	DB	

	DIM A	NO. OF CIRCUITS	PART NO.
YES	71.12[2.800]	28	5-643815-8
YES	68.58[2.700]	27	5-643815-7
YES	66.04[2.600]	26	5-643815-6
YES	63.50[2.500]	25	5-643815-5
YES	60.96[2.400]	24	5-643815-4
YES	58.42[2.300]	23	5-643815-3
YES	55.88[2.200]	22	5-643815-2
YES	53.34[2.100]	21	5-643815-1
YES	50.80[2.000]	20	5-643815-0
YES	48.26[1.900]	19	4-643815-9
YES	45.72[1.800]	18	4-643815-8
YES	43.18[1.700]	17	4-643815-7
YES	40.64[1.600]	16	4-643815-6
YES	38.10[1.500]	15	4-643815-5
YES	35.56[1.400]	14	4-643815-4
YES	33.02[1.300]	13	4-643815-3
YES	30.48[1.200]	12	4-643815-2
YES	27.94[1.100]	11	4-643815-1
YES	25.40[1.000]	10	4-643815-0
YES	22.86[.900]	9	3-643815-9
YES	20.32[.800]	8	3-643815-8
YES	17.78[.700]	7	3-643815-7
YES	15.24[.600]	6	3-643815-6
YES	12.70[.500]	5	3-643815-5
YES	10.16[.400]	4	3-643815-4
YES	7.62[.300]	3	3-643815-3
YES	5.08[.200]	2	3-643815-2
NO	71.12[2.800]	28	2-643815-8
NO	68.58[2.700]	27	2-643815-7
NO	66.04[2.600]	26	2-643815-6
NO	63.50[2.500]	25	2-643815-5
NO	60.96[2.400]	24	2-643815-4
NO	58.42[2.300]	23	2-643815-3
NO	55.88[2.200]	22	2-643815-2
NO	53.34[2.100]	21	2-643815-1
NO	50.80[2.000]	20	2-643815-0
NO	48.26[1.900]	19	1-643815-9
NO	45.72[1.800]	18	1-643815-8
NO	43.18[1.700]	17	1-643815-7
NO	40.64[1.600]	16	1-643815-6
NO	38.10[1.500]	15	1-643815-5
NO	35.56[1.400]	14	1-643815-4
NO	33.02[1.300]	13	1-643815-3
NO	30.48[1.200]	12	1-643815-2
NO	27.94[1.100]	11	1-643815-1
NO	25.40[1.000]	10	1-643815-0
NO	22.86[.900]	9	643815-9
NO	20.32[.800]	8	643815-8
NO	17.78[.700]	7	643815-7
NO	15.24[.600]	6	643815-6
NO	12.70[.500]	5	643815-5
NO	10.16[.400]	4	643815-4
NO	7.62[.300]	3	643815-3
NO	5.08[.200]	2	643815-2
LEADFREE			



- ① MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
 CONTACTS - 0.30[.012] THICK COPPER ALLOY
 BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
 FOR 643815-2 THRU 2-643815-8.
 BRIGHT TIN .00305[.000120] MIN THICKNESS
 FOR 3-643815-2 THRU 5-643815-8.
2. CONTACTS ACCEPT 26 AWG WIRE WITH 1.52[.060] MAX INSULATION DIAMETER.
3. CONTACTS MUST ACCEPT 0.64±0.03[.025] POST AND REMAIN LOCKED IN POSITION.
- ④ IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.
5. DIMENSIONS IN BRACKETS ARE IN INCHES.
6. HOUSING FEATURES ARE: CLOSED END WITH LOCKING RAMP AND WITH POLARIZING TAB.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 11JUN2003	Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES		CHK D. BOSSI 11JUN2003	NAME D. BOSSI 11JUN2003	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.13 [.005] 4 PLC ± ANGLES ± FINISH ①		PRODUCT SPEC 108-1050		RESTRICTED TO -
MATERIAL ①		APPLICATION SPEC 114-1019		SCALE A2
		WEIGHT 00779		DRAWING NO C=643815
		CUSTOMER DRAWING		SHEET 1 OF 1 REV F

A/C BUSINESS GRP. 3323 177-34 'BARRY LEWIS'

643815

A