

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS


**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 751630

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 1958.  
 © COPYRIGHT 1958 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
			C	BECKMAN REV PER P.7000	03-25-81	AKM
			D	OBS. -1 REV G 2588	03-10-87	PAC
			E	REACT. -1 REV G-4619	03-25-88	gjm



FOR 150 TO .230 WIRE INSULATION DIA  
 TONGUE MATERIAL THICKNESS = .040 ± .002

326886	326886-1
PART No.	PT. No. ON TAPE

QTY	DESCRIPTION	MATERIAL AND FINISH	PART NO
1	WIRE TERMINAL ON TAPE	BODY AND SLEEVE: COPPER (90-C-576) TIN PL (MIL-T-10727)	326886-1
1	WIRE TERMINAL	INSULATION: NYLON (MIL-M-20793) TYPE I COLOR: YELLOW	326886

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES ON DECIMALS ± .50 ANGLES

CONTRACT NO: R. BECKMAN 9-23-81  
 DR: R. BECKMAN 9/6/71  
 CHK: R. BECKMAN 9/6/71  
 APPD: R. BECKMAN 9-23-81

NAME: AMP  
 AMP INCORPORATED  
 Harrisburg, Pa.

FINISH	SEE TABLE		
OSGN APPD	OTHER APPD		
SIZE	FSCM NO	DRAWING NO	WIRE SIZE:
B	00779	326886	12-10
SCALE	NTS	SHEET	1 OF 1

CUSTOMER DRAWING