

Distributed by:

**JAMECO**<sup>®</sup>  
ELECTRONICS

**www.Jameco.com ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

Jameco Part Number 753061



LOC		DIST		P		F		ZONE		LTR		REVISIONS			
AD	39											DESCRIPTION	DATE	APPD	
												R	SEE SHEET 1 OF 2	-	-

- ① .000030 GOLD IN LOCALIZED PLATE AREA, .000150 TIN-LEAD ON SOLDER TAILS ALL OVER .000050 NICKEL.
- ② USE .0465±.0010 DRILLED HOLE (#56 DRILL) WITH .001 MIN COPPER.
- ③ CIRCUIT IDENTIFICATION FEATURE OMITTED ON 10 POSITION HEADER ASSEMBLIES.
- ④ DIMENSION APPLIES AT BASE OF SHROUD.
- ⑤ THE NOTED DIMENSIONS APPLY AT THE MATING FACE OF THE HOUSING.
- ⑥  $\text{Y3}$   $\text{Y4}$  ARE LOCATED THE SAME AS  $\text{Y1}$   $\text{Y2}$  EXCEPT ON OPPOSITE SIDE OF HOUSING.
- ⑦ PADS ON THE OPPOSITE SIDE OF THE BOARD TO BE  $\varnothing$ .065 MINIMUM.
- ⑧ REFER TO NO. OF POSN. IN CHART FOR NUMBER OF SURFACES THAT ARE TO BE COPLALAR.
- ⑨ .000030 GOLD IN LOCALIZED PLATE AREA, .000150 TIN ON SOLDER TAILS, ALL OVER .000050 NICKEL.

-	-	.000	.250	5	.430	12	⑨	6-104549-1
.000	1.150	1.150	2.450	49	2.630	100	⑨	6-104549-0
.000	.900	.900	1.950	39	2.130	80	⑨	5-104549-9
.000	.650	.650	1.450	29	1.630	60	⑨	5-104549-8
.025	.525	.525	1.200	24	1.380	50	⑨	5-104549-7
-	.400	.400	.950	19	1.130	40	⑨	5-104549-6
-	.275	.275	.700	14	.880	30	⑨	5-104549-5
-	.225	.225	.600	12	.780	26	⑨	5-104549-4
-	.200	.200	.550	11	.730	24	⑨	5-104549-3
-	.150	.150	.450	9	.630	20	⑨	5-104549-2
.494	-	.025	.200	4	-	10	⑨	5-104549-1
-	-	.000	.250	5	.430	12	①	1-104549-1
.000	1.150	1.150	2.450	49	2.630	100	①	1-104549-0
.000	.900	.900	1.950	39	2.130	80	①	104549-9
.000	.650	.650	1.450	29	1.630	60	①	104549-8
.025	.525	.525	1.200	24	1.380	50	①	104549-7
-	.400	.400	.950	19	1.130	40	①	104549-6
-	.275	.275	.700	14	.880	30	①	104549-5
-	.225	.225	.600	12	.780	26	①	104549-4
-	.200	.200	.550	11	.730	24	①	104549-3
-	.150	.150	.450	9	.630	20	①	104549-2
.494	-	.025	.200	4	-	10	①	104549-1
G	F	E	D	C	B	A	NO. OF POSN	PART NUMBER

OBSOLETE

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± .005 ANGLES ±		DR 07/13/92 R.K. SEIFRIED/UTA CHK 10/23/92 B ELICKER APPD 10/23/92 B ELICKER APPD 10/23/92 B FLINCHBAUGH		AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL HOUSING: PPA COLOR: BLACK CONTACT: PHOSPHOR BRONZE FINISH		PRODUCT SPEC - APPLICATION SPEC -		NAME HEADER ASSEMBLY, W/SIDE & END LATCHES, VERTICAL, SHROUDED, DOUBLE ROW, SURFACE MOUNT, AMPMODU System 50, W/HOLDDOWNS	
SEE TABLE		SIZE D	CAGE CODE 00779	DRAWING NO C= 104549	
		WEIGHT -	SCALE 4:1	SHEET 2 OF 2	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.