



Circuit Diagram

技术特性 Specification

- | | |
|---------|---|
| 1. 规格 | Rating: 2A 250V AC; 4A 125V AC |
| 2. 接触电阻 | Contact R: 50 mΩMax |
| 3. 绝缘电阻 | Insulation R: DC 500V 1000MΩ Min |
| 4. 耐压 | Dielectric strength: AC 1500V, 1 Minute |
| 5. 操作温度 | Operating temperature: -20C ~ +65C |
| 6. 电气寿命 | Electrical life: 10,000 Cycles |

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.	
DRAWN: Colin Hung		JAMECO NO. 76241	GOLDSUN NO. TS-1307
VERIFY PEOPLE:		Description Toggle Switch Full Single Pole Single Throw (On-Off) Solder 125VDC @ 4 Amp 1/2 Inch Mounting	
		UNIT: mm	SCALE: SHEET 1 OF 1
		CAS No: ERN No:	
		Rev. 1	