





Date	Rev.	Description

	PARTS NAME	MATERIAL	ELECTROPLATING	RoHS
1	Slide Handle	Brass	Chromium Plating	RoHS
2	Spring	Steel wire	-----	RoHS
3	Bushing	Brass	Nickel Plating	RoHS
4	Supporting Halt	Brass	-----	RoHS
5	Sliding Point	Bakelite	-----	RoHS
6	Housing	Bakelite	-----	RoHS
7	Movable Plate	Brass	Silver Plating	RoHS
8	Terminals	Brass	Silver Plating	RoHS
9	Nuts	Brass	Nickel Plating	RoHS
10	Zigzag Washer	Stainless Steel	-----	RoHS
11	Fix Washer	Stainless Steel	-----	RoHS
12	Steel crust	Stainless Steel	-----	RoHS
13	Epoxy Seal	5010A/B	-----	RoHS



Circuit Diagram

Specification

Rating: 2A 250V AC ;5A 125V AC  
 Contact R: 20 mΩ Max  
 Insulation R: DC500V 1000MΩ Min  
 Dielectric strength: 1500V AC, 1minute  
 Electrical life: 10,000 Cycles

MATERIAL		<b>GOLDSUN ELECTRONICS CO., LTD.</b>		
DRAWN: Ivan Wang		JAMECO NO. 76523-10	GOLDSUN NO. GS-101	
VERIFY PEOPLE: Jenny		Description MINI TOGGLE SWITCH ON-OFF SPST 2P SOLDER LUGS		Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No:	ERN No:

DCC. NO.
A4 DRAWING NO.