

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 843008

REVISIONS

CTR	DESCRIPTION	DATE	APPROVED
C	REVISION REVISED TAPE NO. B-630	4-1-70	FCY
D	REV/6726-0066-93	4-8-93	70/mc

©1957 BY AMP, INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.



FOR .105 TO .150 WIRE INSULATION DIA.
TONGUE MATERIAL THK = .031 ±.002

100	LOOSE PC, BOX	8-324159-1	
1	324159 ON TAPE	2-324159-2	BODY & SLEEVE: COPPER (QQ-C-576) TIN PL (MIL-T-10727)
1	WIRE TERMINAL	324159	INSULATION: NYLON (MIL-M-20593) TYPET COLOR: BLUE
QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON DECIMALS: ±.008 ANGLES: ±.5°			
MATERIAL		CONTACT NO. DR. <i>117</i> 3-20-70 DR. <i>117</i> 3-20-70 CHK. <i>117</i> 3-20-70 APPD. <i>117</i> 3-20-70 REL. <i>117</i> 3-20-70 DESGN. <i>117</i> 3-20-70 OTHER APPD.	
SEE TABLE		NAME: AMP INCORPORATED WIRE TERMINAL P.I.D.G-RINGS TONGUE WIRE SIZE: 16-14 SIZE: 00779 SCALE: 1:1 SHEET: 1 OF 1	