

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 844633

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			DAP		
G	14	P	LTR	DESCRIPTION	DATE	DWN	APVD
		M		REV PER 0G3A-0269-04	08APR04	JR	MS

AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- △1 STAMP AMP 16-14* APPROX AS SHOWN
- △2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- △3 MATERIAL: COPPER PER ASTM B-152 ANNEALED
- △4 FINISH: TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545
- △5 FINISH: TIN/LEAD (60/40) PLATE, .000100 MIN THK PER MIL-P-81728
- △6 COLOR CODED BLACK OVER BRAZED SEAM TO DENOTE 60/40 TIN-LEAD PLATING

△4	100	LOOSE PIECE, BOX	8-34137-1
△5 △6	----	LOOSE PIECE	34137-1
△4	----	LOOSE PIECE	34137
FINISH	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS 1-800-522-6752	PRODUCT INFORMATION CENTER	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION 1-800-722-1111	TOOLING ASSISTANCE CENTER	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] SOLID OR STRANDED
FOR ORDER ENTRY 1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-13-93	Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES		CHK DA PATTERSON 4-13-93	NAME SPLICE, PARALLEL, SOLISTRAND	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD DA PATTERSON 4-13-93	PRODUCT SPEC -	APPLICATION SPEC -
MATERIAL - △3	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 10:1	DRAWING NO C=34137	RESTRICTED TO -
		SHEET 1	OF 1	REV M