

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 940457


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14	K	REV / 0720-0584-95	11APR95	MLE SB

AMP WIRE RANGE	E13288	LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



STYLE I



STYLE II

1. WIRE INSUL DIA,
3.81-6.35 [.150-.250]

STYLE	QTY	PACKAGE TYPE	PART NO
I	50	LOOSE PIECE, BOX	8-34945-2
II	2000	ON TAPE, REEL	2-34945-2
II	500	LOOSE PIECE	2-34945-1
I	500	LOOSE PIECE	34945

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE:
90°C [194°F]

VOLTAGE RATING:
600V MAX
1000V (FIXTURES OR SIGNS)

CIRCULAR MIL AREA:
2.62mm²-6.64mm² [5180-13100]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED.
mm [in]	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
ANGLES	±-

MATERIAL: BODY, CU ASTM B 152
PVC, COLOR, YELLOW

FINISH: TIN PLATE
PER MIL-T-10727

DWN	M ELLIS	03APR95	AMP AMP Incorporated Harrisburg, PA 17105-3608
CHK	C PRESNELL	03APR95	
APVD	S BORTNER	03APR95	
PRODUCT SPEC	UL486A		
APPLICATION SPEC	-		NAME SPLICE, BUTT, PLASTI-GRIP™, WIRE SIZE, 12-10 AWG
WEIGHT	-		SIZE A3
CUSTOMER DRAWING			CAGE CODE 00779
			DRAWING NO C-34945
			SCALE 4:1
			SHEET 1 OF 1
			REV K