

Enclosed Switching AC-to-DC Power Supplies



Jameco carries the full line of Mean Well Power products. For additional products visit www.Jameco.com/meanwellproducts



Enclosed Switching AC-to-DC Power Supplies (Continued)



PSP-500
*Web Code: EPS

Part No.	Manufacturer	Mfr. Part No.	Output		Size (L"xW"xH")	Ripple & Noise (mV p-p)*	Load Reg. (±%)*	Line Reg. (±%)*	Additional Info Pg. 128†	Certification	Pricing		
			Voltage @ Current (min-max)	Power							1	5	25
Single Output (Continued)													
201971	Mean Well	S-100F-24	+24V @ 0-4.5A	108W	7.8x3.9x1.5	150	0.5	0.5	2	UL/TUV/CE/CB	\$32.95	\$26.95	\$23.95
323732	Mean Well	RS-100-24	+24V @ 0-4.5A	108W	6.3x3.8x1.5	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	39.95	32.95	26.95
155651	Power One	MAP110-1024CM	+24V @ 5A or +28V @ 4.3A	110W	7.0x4.3x1.8	240	0.5	1.0	—	UL/CSA/TUV	29.95	26.95	24.95
1945920	APS	RP1150-24C	+24V @ 0-6.25A	150W	7.5x4.2x2.0	100	1.0	1.0	—	UL/CE	34.95	29.95	26.95
173404	Mean Well	SP-150-24	+24V @ 0-6.25A	150W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	56.95	49.95	44.95
371012	Potrans	GL150W-24-NC	+24V @ 6.5A	156W	7.8x3.7x2.5	180	2.0	2.0	—	UL/CUL/TUV/CE	26.95	23.95	21.49
123450	Mean Well	S-150-24	+24V @ 0-6.5A	156W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
2079429	PowerLD	PD-150-24	+24V @ 0-6.5A	156W	7.8x3.9x1.5	120	1.0	0.5	—	UL/CUL/CE	35.95	32.95	29.95
323855	Mean Well	RS-150-24	+24V @ 0-6.5A	156W	7.8x3.9x1.5	120	0.5	0.5	1	UL/CUL/TUV/CE/CB	39.95	34.95	29.95
2094864	Mean Well	HRPG-150-24	+24V @ 0-6.5A	156W	6.3x3.8x1.5	150	0.5	0.3	6	UL/CUL/TUV/CE/CB/PFC	84.95	79.95	74.95
194782	Mean Well	SP-200-24	+24V @ 0-8.4A	201.6W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	62.95	58.95	54.95
137657	Mean Well	S-240-24	+24V @ 0-10A	240W	7.5x3.7x2.6	180	0.5	0.5	2	UL/CUL/TUV/CE/CB/PFC	79.95	74.95	69.95
2101518	Mean Well	SP-240-24	+24V @ 0-10A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
196657	Mean Well	S-320-24	+24V @ 0-12.5A	300W	8.5x4.5x2.0	150	0.5	0.5	2	UL/CUL	69.95	64.95	59.95
244752	Mean Well	SP-320-24	+24V @ 0-13.0A @ 230VAC; 0-10.4A @ 115VAC	312W	8.5x4.5x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	74.95	69.95	64.95
2102220	Mean Well	HRP-300-24	+24V @ 0-14A	336W	7.7x4.1x1.6	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	114.95	104.95	94.95
2094881	Mean Well	HRPG-300-24	+24V @ 0-14A	336W	7.7x4.1x1.6	150	0.5	0.3	6	UL/CUL/TUV/CE/CB/PFC	119.95	114.95	109.95
2101606	Mean Well	SE-450-24	+24V @ 0-18.8A	451.2W	8.9x4.9x2.0	200	0.5	0.2	—	UL/CUL	99.95	92.95	86.95
301322	Mean Well	SP-480-24	+24V @ 0-20.0A @ 230VAC; 0-18A @ 115VAC	480W	10.9x5.0x1.7	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	154.95	144.95	134.95
147054	Mean Well	SP-500-24	+24V @ 0-20.0A @ 230VAC; 0-17A @ 115VAC	480W	6.7x4.7x3.7	240	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	149.95	139.95	129.95
295902	Mean Well	SE-600-24	+24V @ 0-25A	600W	9.7x5.0x2.5	150	0.5	0.5	2	UL/CUL	114.95	106.95	99.95
374231	Mean Well	PSP-600-24	+24V @ 0-25A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	139.95	125.95
320048	Mean Well	SP-750-24	+24V @ 0-31.3A	750W	10.9x5.0x2.5	120	0.5	0.2	3	UL/CUL/TUV/CE/CB	219.95	199.95	184.95
374310	Mean Well	SCP-800-24	+24V @ 0-33A	792W	11.4x4.7x2.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB	229.95	209.95	199.95
1585717	Mean Well	RSP-1000-24	+24V @ 0-40A	960W	11.6x5.0x1.6	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	319.95	299.95	279.95
2101569	Mean Well	RE-1000-24	+24V @ 0-41.7A	1000.8W	10.9x5.0x2.5	200	0.5	0.5	4	UL/CUL	209.95	184.95	164.95
373923	Mean Well	PSP-1500-24	+24V @ 0-56.4A	1353.6W	10.9x5.1x7.5	150	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	449.95	424.95	399.95
2103353	Mean Well	SE-1500-24	+24V @ 0-62.5A	1500W	10.9x6.9x2.5	150	0.5	0.5	—	UL/CUL	369.95	332.95	299.95
694938	Mean Well	RSP-1500-24	+24V @ 0-63A	1512W	10.9x5.0x3.3	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	424.95	389.95	359.95
693409	Mean Well	SP-75-27	+27V @ 0-2.8A	75.6W	7.0x3.9x1.3	100	0.5	0.5	3	UL/CUL/TUV/CE/CB	42.95	36.95	31.95
202033	Mean Well	S-150-27	+27V @ 0-5.6A	151.2W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
693513	Mean Well	SP-150-27	+27V @ 0-5.6A	151.2W	7.8x3.9x2.0	150	0.5	0.5	—	UL/CUL/TUV/CE/CB/PFC	56.95	49.95	44.95
693548	Mean Well	SP-200-27	+27V @ 0-7.5A	202.5W	7.0x3.9x2.0	150	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	62.95	58.95	54.95
693581	Mean Well	S-320-27	+27V @ 0-11.0A	297W	8.5x4.5x2.0	200	0.5	0.5	2	UL/CUL	69.95	64.95	59.95
693628	Mean Well	SP-320-27	+27V @ 0-11.7A	315.9W	8.5x4.5x2.0	200	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	74.95	69.95	64.95
190706	Mean Well	SP-500-27	+27V @ 0-18A @ 230VAC; 0-15.3A @ 115VAC	486W	6.7x4.7x3.7	200	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	149.95	139.95	129.95
295911	Mean Well	SE-600-27	+27V @ 0-22.2A	599.4W	9.7x5.0x2.5	150	0.5	0.5	2	UL/CUL	114.95	106.95	99.95
374257	Mean Well	PSP-600-27	+27V @ 0-22.2A	600W	6.7x4.7x3.7	240	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	149.95	139.95	125.95
374038	Mean Well	SP-750-27	+27V @ 0-27.8A	750W	10.9x5.0x2.5	120	0.5	0.2	3	UL/CUL/TUV/CE/CB	219.95	199.95	184.95
231652	Mean Well	PSP-1000-27	+27V @ 0-33.6A @ 230VAC; 0-28.6A @ 115VAC	907.2W	10.9x5.1x5.0	150	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	419.95	374.95	344.95
1585709	Mean Well	RSP-1000-27	+27V @ 0-37.0A	999W	11.6x5.0x1.6	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	319.95	299.95	279.95
231714	Mean Well	PSP-1500-27	+27V @ 0-50.4A	1360.8W	10.9x5.1x7.5	150	0.5	0.2	5	UL/CUL/TUV/CE/CB/PFC	449.95	424.95	399.95
694946	Mean Well	RSP-1500-27	+27V @ 0-56.0A	1512W	10.9x5.0x3.3	150	0.5	0.5	5	UL/CUL/TUV/CE/CB/PFC	424.95	389.95	359.95
392834	Mean Well	S-240-30	+30V @ 0-8A	240W	7.5x3.7x2.6	180	0.5	0.5	2	UL/CUL/TUV/CE/CB/PFC	74.95	69.95	66.95
2102473	Mean Well	SP-240-30	+30V @ 0-8A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
2101753	Mean Well	HRPG-600-36	+36V @ 0-17.5A	630W	8.6x4.1x2.5	200	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	189.95	174.95	164.95
693249	Mean Well	RS-50-48	+48V @ 0-1.1A	52.8W	3.9x3.8x1.4	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	23.95	19.95	16.95
216805	Mean Well	SP-75-48	+48V @ 0-1.6A	76.8W	7.0x3.9x1.3	100	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	42.95	36.95	31.95
216793	Mean Well	S-100F-48	+48V @ 0-2.2A	105.6W	7.8x3.9x1.5	150	0.5	0.5	2	UL/TUV/CE/CB	32.95	26.95	23.95
167346	Mean Well	S-150-48	+48V @ 0-3.2A	153.6W	7.0x4.3x2.0	240	0.2	0.2	2	UL/CUL/TUV/CE/CB	34.95	32.49	29.95
201929	Mean Well	SP-150-48	+48V @ 0-3.2A	154W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE	39.95	35.95	32.95
201930	Mean Well	SP-150-48	+48V @ 0-3.2A	153.6W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	56.95	49.95	44.95
323863	Mean Well	RS-150-48	+48V @ 0-3.3A	158.4W	7.8x3.9x1.5	200	0.5	0.5	1	UL/CUL/TUV/CE/CB	39.95	34.95	29.95
202068	Mean Well	SP-200-48	+48V @ 0-4.2A	201.6W	7.0x3.9x2.0	250	0.5	0.5	3	UL/CUL/TUV/CE/CB/PFC	62.95	58.95	54.95
2102481	Mean Well	SP-240-48	+48V @ 0-5A	240W	7.5x3.7x2.0	150	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	64.95	59.95	55.95
689776	Metapo	1M321C48-0M	+48V @ 0-6.5A	312W	7.5x4.5x2.0	240	0.5	0.5	—	UL/CUL	64.95	59.95	54.95
207191	Mean Well	S-320-48	+48V @ 0-6.5A	312W	8.5x4.5x2.0	240	0.5	0.5	2	UL/CUL	69.95	64.95	59.95
244770	Mean Well	SP-320-48	+48V @ 0-6.7A @ 230VAC; 0-5.4A @ 115VAC	321.6W	8.5x4.5x2.0	240	0.5	0.2	3	UL/CUL/TUV/CE/CB/PFC	74.95	69.95	64.95
2105164	Mean Well	SE-450-48	+48V @ 0-9.4A	451.2W	8.9x4.9x2.0	200	0.5	0.2	—	UL/CUL	99.95	92.95	86.95

*Primary Output

More Enclosed Switching Power Supplies on page 127-129 & 131-132

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 189.

