

AC-to-DC Regulated Switching Wall Adapters

4 LEVELS OF SAVINGS
 NAME BRANDS HOUSE BRANDS FACTORY OVERRUN DOLLAR SALE


Jameco carries the full line of Mean Well products. For additional Mean Well products visit www.Jameco.com/meanwellproducts



AC-to-DC Regulated Switching Wall Adapters

*Web Code: CDZ

We specialize in Wall Adapters – Call for additional OEM PRICING.



We are happy to change any listed DC wall adapter power plug to a connector of your choice (see pg 114) for just \$2.50 each. A 100 pc. minimum order applies.

NEW
 MARKED IN PINK



Part No.	Manufacturer	Product No.	Output Rating		Output Connector ID x OD mm Female/Male; Polarity ◆	Input VAC @ Hz	Size (H" x W" x D")	Case Color	Output Cord Length	Wt. (lbs.)	Agency Approvals	Pricing			
			Volt. (VDC)	Current (mA)								1	10	50	100
2126125	OEM	ADS0051-W050080*	5	800	2.1mm x 5.5mm F 2	100-240@50-60	1.9 x 1.6 x 0.9	Black	6'	0.1	UL/CUL/CE/CEC	\$7.95	\$6.95	\$6.25	\$5.95
2135531	ReliaPro	LD-008*	5	1000	2.1mm x 5.5mm F 2	100-240@50-60	2.3 x 1.6 x 0.9	Black	4'	0.2	CE	8.95	7.95	6.95	6.49
1940660	Mean Well	GS06U1P1J*	5	1000	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CEC	11.95	10.95	9.95	8.95
1950981	Philips	AY3192/17	5	2000	1.7mm x 4.0mm F 2	100-240@50-60	3.1 x 1.4 x 1.3	Black	6'	0.3	UL/CUL	10.95	9.95	8.95	7.95
157340	D-Link	AF1205B	5	2000	2.1mm x 5.5mm right angle F 2	100-120@50-60	2.4 x 1.4 x 1.1	Black	6'	0.3	UL/CUL/TUV	7.95	6.95	5.49	3.95
210894	ReliaPro	SYS1193-1005*	5	2000	2.1mm x 5.5mm F 2	100-240@47-63	2.9 x 1.4 x 2.2	Black	6'	0.2	UL/CUL	12.95	11.49	10.49	9.49
1940740	Mean Well	GS12U05P11	5	2000	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	4'	0.3	UL/CUL/CEC	12.95	11.49	10.49	9.49
2129641	ELPAC	WM1005-760**	5	2000	2.5mm x 5.5mm F 2	100-120@50-60	2.8 x 1.6 x 1.1	Black	6'	0.3	UL/CUL	10.95	9.95	8.95	7.95
1954199	Mean Well	GS15U-1P1J*	5	2400	2.1mm x 5.5mm F 2	90-264@47-63	2.8 x 1.3 x 2.0	Black	6'	0.4	UL/CUL/CEC	14.95	13.49	11.95	10.95
2135419	DVE	DSA-0151A-05A	5	2400	2.1mm x 5.5mm F 2	100-120@50-60	3.0 x 2.0 x 1.3	Black	6'	0.3	UL/CUL	11.95	10.95	9.95	8.95
689864	ReliaPro	DSA-0151A-05	5	2400	2.5mm x 5.5mm right angle F 2	100-240@50-60	3.2 x 2.1 x 1.4	Black	6'	0.5	UL/CUL	14.95	13.95	12.95	11.95
1952863	Mean Well	GS18U05-P1J	5	3000	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	4'	0.5	UL/CUL/CEC	15.95	14.95	13.95	12.95
379623	Mean Well	GS25U05-P1J	5	4000	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	15.95	14.95	13.95	12.95
2135451	Open Peak	LFS054000D-A8S*	5	4000	2.1mm x 5.5mm right angle F 2	90-132@60	3.3 x 2.0 x 1.5	Black	6'	0.3	UL/CUL/CEC	13.95	12.95	11.95	10.95
2082011	Friwo	MPA3U	6	400	2.1mm x 5.5mm right angle F 2	100-240@50-60	2.8 x 2.0 x 0.7	Black	6'	0.3	UL/CUL	5.95	5.49	4.95	3.95
1940678	Mean Well	GS06U-11P1J*	7.5	800	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CEC	11.95	10.95	9.95	8.95
1940758	Mean Well	GS12U07/P11	7.5	1600	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	6'	0.3	UL/CUL/CEC	12.95	11.49	10.49	9.49
1940686	Mean Well	GS06U-2P1J*	9	660	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CEC	11.95	10.95	9.95	8.95
2099850	Ault	HES12-090130	9	1300	2.1mm x 5.5mm F 2	100-240@50-60	2.4 x 1.8 x 1.3	Black	6'	0.3	UL/CUL/CE	11.95	10.95	9.95	8.95
2135591	Unifive	US100913*	9	1300	2.5mm x 5.5mm F 2	100-240@50-60	2.4 x 1.7 x 1.1	Black	6'	0.2	UL/CUL	11.95	10.95	9.95	8.95
1940766	Mean Well	GS12U09-P11	9	1330	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	6'	0.3	UL/CUL	12.95	11.49	10.49	9.49
1952847	Mean Well	GS18U09-P1J	9	2000	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	15.95	14.95	13.95	12.95
380140	Mean Well	GS25U09-P1J	9	2780	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	17.95	15.95	14.49	12.95
2121578	ReliaPro	ST-12500	12	500	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.3	UL/CUL/CEC	9.95	8.95	7.95	6.95
1940694	Mean Well	GS06U-3P1J*	12	500	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CE	11.95	10.95	9.95	8.95
1955036	Arndt	26092#	12	700	2.1mm x 5.5mm F 2	95-240@47-63	4.0 x 2.3 x 1.1	Black	5.5'	0.4	UL/CUL	10.95	9.95	8.95	6.95
2129668	ELPAC	WM1012-760**	12	800	2.5mm x 5.5mm F 2	100-120@50-60	2.8 x 1.6 x 1.1	Black	6'	0.3	UL/CUL	10.95	9.95	8.95	7.95
2121586	ReliaPro	ST-121A	12	1000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.3	UL/CUL/CEC	11.95	10.95	9.95	8.95
1940774	Mean Well	GS12U12-P11	12	1000	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	6'	0.3	UL/CUL/CEC	12.95	11.49	10.49	9.49
1954201	Mean Well	GS15U-3P1J*	12	1250	2.1mm x 5.5mm F 2	90-264@47-63	2.8 x 1.3 x 2.0	Black	6'	0.4	UL/CUL/CE	15.95	14.49	12.95	11.49
2126002	ITE Power	S018BU1200150	12	1500	2.1mm x 5.5mm F 2	100-240@50-60	2.9 x 1.7 x 1.2	Black	6'	0.3	UL/CUL	12.95	11.49	9.95	8.95
1952855	Mean Well	GS18U12-P1J	12	1500	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.2	UL/CUL/CE/CEC	15.95	14.95	13.95	12.95
2082134	ReliaPro	ST-122A	12	2000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.4	UL/CUL/CEC	14.95	13.49	11.95	10.95
1950497	ReliaPro	SYS1308-2412*	12	2000	2.1mm x 5.5mm F 2	100-240@50-60	2.9 x 1.3 x 1.7	Black	6'	0.4	UL/CUL/CEC	15.95	14.49	12.95	11.49
380156	Mean Well	GS25U12-P1J	12	2080	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CE/CEC	16.49	14.95	13.49	12.49
1940707	Mean Well	GS06U-4P1J*	15	400	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CEC	11.95	10.95	9.95	8.95
1952871	Mean Well	GS18U15-P1J	15	1200	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.4	Black	6'	0.4	UL/CUL/CE/CEC	15.95	14.95	13.95	12.95
380173	Mean Well	GS25U15-P1J	15	1670	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CE	16.49	14.95	13.49	12.49
1940715	Mean Well	GS06U-5P1J*	18	330	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.3 x 1.9	Black	6'	0.2	UL/CUL/CEC	11.95	10.95	9.95	8.95
1940791	Mean Well	GS12U18-P11	18	670	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	6'	0.3	UL/CUL/CEC	12.95	11.49	10.49	9.49
380191	Mean Well	GS25U18-P1J	18	1380	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 1.2 x 1.3	Black	6'	0.5	UL/CUL/CEC	16.49	14.95	13.49	12.49
2129650	ELPAC	WM1024-760**	24	400	2.5mm x 5.5mm F 2	100-120@50-60	2.8 x 1.6 x 1.1	Black	6'	0.3	UL/CUL	10.95	9.95	8.95	7.95
1940803	Mean Well	GS12U24-P11	24	500	2.1mm x 5.5mm F 2	90-264@47-63	2.6 x 1.9 x 1.0	Black	6'	0.3	UL/CUL/CEC	12.95	11.49	10.49	9.49
1952898	Mean Well	GS18U24-P1J	24	750	2.1mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	15.95	14.95	13.95	12.95
2121594	ReliaPro	ST-241A	24	1000	Screw terminals	100-240@50-60	3.8 x 2.1 x 1.6	Black	—	0.3	UL/CUL/CEC	14.95	13.49	11.95	10.95
380202	Mean Well	GS25U24-P1J	24	1040	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	16.49	14.95	13.49	12.49
380220	Mean Well	GS25U28-P1J	28	890	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.3	Black	6'	0.6	UL/CUL/CEC	16.49	14.95	13.49	12.49
380412	Mean Well	ES25U36-P1M	36	690	2.5mm x 5.5mm F 2	90-264@47-63	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CE	16.49	14.95	13.49	12.49
380244	Mean Well	GS25U48-P1J	48	520	2.1mm x 5.5mm F 2	100-240@50-60	3.1 x 2.1 x 1.3	Black	6'	0.5	UL/CUL/CEC	16.49	14.95	13.49	12.49

* Slimline package ** RFI filter on cord # With light indicator CEC

RoHS compliant product + This product is available in both RoHS and non-RoHS versions. Add an "R" before part number for RoHS version. Details on page 183.